






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/12/2020	PHOSPODAR



PART NUMBER	ATTENUATION	BACK REFLECTION
FOATSC-31-05D	5dB	≤ -55dB
FOATSC-31-10D	10dB	≤ -55dB
FOATSC-31-15D	15dB	≤ -55dB
FOATSC-31-20D	20dB	≤ -55dB

- NOTES:
1. SC ATTENUATOR UTILIZES "PC" POLISH.
  2. ATTENUATOR IS PACKAGED TWO WITH DUST CAPS INSTALLED (NOT SHOWN).
  3. OPERATING TEMPERATURE RANGE: -40° C TO +75° C.
  4. SINGLE MODE WAVELENGTH RANGE: 1310 nm.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [.5]      ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY DFRISIELLO CHECKED BY PHOSPODAR APPROVED BY PHOSPODAR	DATE 11/12/2020 11/12/2020 11/12/2020	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY <b>FIBER OPTICS</b>
SIZE <b>A</b>		CAGE CODE <b>43321</b>	ITEM NO. <b>FOATSC-31</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: FOATSC-31.SLDDRW		SHEET 1 OF 1