





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B3		See PCN E-20-017532	30NOV2020	NR	CS
B4		GAP SIZE TOL ADDED	21SEP2021	SA	CS
B5		CHANGE BASE OF DIM 1.51 TO 1.53. ADDED TOL TO DIM 7.12 AND 1.8	11DEC2025	DK	CS



NOTES

Bemerkungen




- 1

SILVER IN CONTACT AREA
Silber in Kontaktbereich
- 2

TIN IN CRIMP AREA
Sn im Crimpbereich
- 3

PACKAGING: PRODUCT REELED ON CORRUGATED REEL WITH INTERLEAVING PAPER
SIX REELS PER CORRUGATED SHIPPING BOX. QUANTITY: 30000 PCS./REEL.
Verpackung: Spulenware auf Wellpappespule mit Zwischenlagenpapier
Sechs Spulen pro Versandkarton. Stueckzahl: 30000 Teile/Spule
- 4

CONDITION AS DELIVERY
Auslieferungszustand





- 5

REVISION MARKING AND MANUFACTURING LOCATION CODE
Revision Stempel und Produktionsstandort
- 6

LISTED WEIGHT INCLUDE THE CARRIER STRIP
Gewicht inklusive Traegerstreifen
- 7

APPLICATOR PN SEE IN APPLICATION SPEC. 114-94413
PN des Applicators siehe in Verarbeitungsspec. 114-94413
- 8

MICROSECTION FOR CRIMPINSPECTION HAVE TO BE
DONE ON SHOWN POSITION
Schliffbild zur Crimpüberwachung ist bei angezeigter
Position durchzuführen



RTK031	0.35mm ²		CuSn	B	2298121-1
CABLE TYPE	WIRE RANGE	FINISH	MATERIAL	REV	PART NO
TE Connectivity					
NAME MATE-AX, SOCKET CENTER CONTACT, 180 DEGREES, RTK031					
SIZE CAGE CODE DRAWING NO RESTRICTED TO					
SCALE 20:1 SHEET 1 OF 1 REV B5					

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. De Cloet CHK O. De Cloet APVD K. Schrethling
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	29SEP2016
mm	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ±	29SEP2016
	ANGLES FINISH	108-94515
MATERIAL see table	-	APPLICATION SPEC
-	-	WEIGHT 0.038 g/6
CUSTOMER DRAWING		7