






This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of AAOR. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of AAOR. © 2019 AAOR




UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION 		 Amphenol Aorora Technology (Huizhou) Co.,Ltd										
X.	±0.35	X.	± 5°	DOC TYP	Customer Drawing		TITLE: FlexFast™ Duo CONNECTOR K07R SERIES P1.8 Receptacle 48pin									
X.X	±0.25	X.X	± 4°													
X.XX	±0.20	X.XX	± 3°													
X.XXX	±0.10	X.XXX	± 2°													
LINEAR DIMS		ANGLES DIMS														
DWG NO.: A-S0925				DESIGN	DATE		Hanson 2024-01-20		SIZE	PART NUMBER: K07R-DRFA5-6*P48		REV. A				
MATERIAL		SEE NOTES														
FINISHED		SEE NOTES														
				APPROVED	DATE		Sam 2024-01-20		SCALE		1:1		UNIT : mm		SHEET 2 OF 3	









NOTES:

1. MATERIAL:
1.1 CARRY TAPE:PS,T=0.40±0.05MM,CLEAR
1.2 REEL: HIPS; 1.3 SHIM:PE,CLEAR
2. PRIMARY PACKING: SEE DRAWINGS(AS FOLLOWS)
3. SECONDARY PACKING:150PCS/REEL;
4 REELS/CARTON(600PCS/CARTON).
4. PEELING RESISTANCE:0.1~0.7N(10~70GF); PEELING ANGLE: 165°~180°; PEELING SPEED:300MM/MINUTES.



DETAIL:A
SCALE:2:1



UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION		 Amphenol Aorora Technology (Huizhou) Co.,Ltd						
X.	±0.35	X. °	± 1°			TITLE: FlexFast™ Duo CONNECTOR K07R SERIES P1.8 Receptacle 48pin						
X.X	±0.25	X.X °	± 0.5°									
X.XX	±0.20	X.XX °	± 0.5°									
X.XXX	±0.10	X.XXX °	± 1°									
LINEAR DIMS		ANGLES DIMS										
DWG NO.: A-S0925				DOC TYP		Customer Drawing						
MATERIAL		SEE NOTES		DRAWN	DATE	Hanson			SIZE	PART NUMBER		REV.
					2024-01-20							
FINISHED		SEE NOTES		DESIGN	DATE	Hanson			A4	K07R-DRFA5-6*P48		A
					2024-01-20							
				CHECKED	DATE	Elven						
					2024-01-20				SCALE		1:1	UNIT : mm
				APPROVED	DATE	Sam						
					2024-01-20							