



RECOMMENDED PCB LAYOUT

N = Number of poles
Dim A = N x 5.0
Dim B = (N - 1) x 5.0

	Dim A	Dim B
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	02/09'06	Part No. is changed.	Marvin
△	06/22'06	Safety is changed from UL 250V/16A to cULus 300V/15A	Marvin
△	08/01'06	cULus Solid wire and Stranded wire is changed.	Marvin
△	04/03'10	Part No. is changed.	Tason
△	09/27'10	Wire range is changed from 0.75-1.5mm ² to 0.5-1.5mm ²	Tason
△	05/11'11	The dimension is changed from 9.9mm to 10.0mm	Tason
△	05/11'11	Change here	Tason
△	05/11'11	The CSA spec is removed	Tason
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Terminal body: Brass(CuZn), Tin plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Wire guard: Stainless steel
- Item ④ Terminal housing: Thermoplastic (UL94V-0)

Electrical cULus/VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 15A/17.5A
- Wire range: 0.5-1.5mm²
- Solid wire(AWG): 14-22/14-22
- Stranded wire(AWG): 14-22/14-22
- Torque: 2.6Lb-In/0.4Nm
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- SAFETY APPROVAL DATA: cULus VDE △
- Critical dimension: △

TC xx 0 3 x x xxxx G △

POLES	COLOR	DIM C Length	
02 02 CONTACTS	0 BLACK	0 4.4mm	000 0 Standard @ logo
03 03 CONTACTS	5 GREEN(RAL6018/T)	1 3.8mm	000 A Standard ANY logo
...	6 BLUE	2 3.5mm	Any special item by
24 24 CONTACTS	8 GREY(RAL7035/D)	3 2.9mm	customer request,
	C GREEN (RAL6018/U)		please contact sales
			department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TC-5.0 Series 2-Interlock							
PART NO.		TCxx03xxxxxxG 			DWG NO.	8TC0061			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Tason 2011.05.11	Tason 2010.04.03					UNIT: mm	X. ±0.50
								SCALE: NONE	X.X ±0.30
					SHEET: 01/01	REV: D	X.XX ±0.10		
							X° ±1°		