




IN THE CONSTANT PURPOSE OF IMPROVING ITS PRODUCTS, Amphenol Socapex RESERVES THE RIGHT TO MODIFY ANY DIMENSION OR CHARACTERISTICS.
FM.NPD.0076.THYZE.PUNE rev B



MDP FTV 7 X X


Codage A ou B
Coding A or B

G: Protection cadmium vert olive (non RoHS)
Olive drab cadmium plating (not RoHS)

N: Protection nickel (RoHS)
Nickel plating (RoHS)


ZN: Protection zinc nickel noir (RoHS)
Black zinc nickel plating (RoHS)

Pin assignments				
MDP 1		MDP 2		
Signal type	N° pin	N° pin	Signal type	
GND	1	8	GND	
Out	3	12	In	
	5	10		
GND	7	13	GND	
Out	9	17	In	
	11	15		
GND	13	7	GND	
Out	15	11	In	
	17	9		
GND	19	19	GND	
In	2	2	Out	
CFG	4	4	CFG	
CFG	6	6	CFG	
GND	8	1	GND	
Out	10	5	In	
	12	3		
GND	14	14	GND	
I/O	16	16	I/O	
	18	18		
PWR out	20	20	PWR out	



Perçage panneau
Panel drilling

Ø 25,65^{+0,25}₀
[1,0098^{+0,0098}_{-0,0000}]



Produit utilisable avec un cordon mâle Mini Display Port
Product usable with male Mini Display Port cordset

Dimensions are in mm / [inch]

APPROVAL FOR MANUFACTURING Add missing specifications on the drawing if necessary (specific labellings, tolerances,...)		DRAWN BY : S. FALCOZ		UPDATED BY:		LAST APPROVED BY: M. RINSANT	
CUSTOMER : PROGRAM : Name : Date :		ALL DIMENSIONS ARE IN MM SCALE : 2,0		AMPHENOL SOCAPEX B.P. 29 74311 THYZE CEDEX		ORIGINAL DRAWING DATE : 14/12/22 REV : A CONFIGURATION DATA ARE AVAILABLE IN PDM PAGE : 1/1	
CUSTOMER SIGNATURE						191-PLC-1199-00	