




Recommended PCB Layout

No. of Contacts	Dimensions	
	A	B
2	2.0	4.0
3	4.0	6.0
4	6.0	8.0
5	8.0	10.0
6	10.0	12.0
7	12.0	14.0
8	14.0	16.0
9	16.0	18.0
10	18.0	20.0
11	20.0	22.0
12	22.0	24.0
13	24.0	26.0
14	26.0	28.0
15	28.0	30.0
16	30.0	32.0
17	32.0	34.0
18	34.0	36.0
19	36.0	38.0
20	38.0	40.0

No. of Contacts	Dimensions	
	A	B
21	40.0	42.0
22	42.0	44.0
23	44.0	46.0
24	46.0	48.0
25	48.0	50.0
26	50.0	52.0
27	52.0	54.0
28	54.0	56.0
29	56.0	58.0
30	58.0	60.0
31	60.0	62.0
32	62.0	64.0
33	64.0	66.0
34	66.0	68.0
35	68.0	70.0
36	70.0	72.0
37	72.0	74.0
38	74.0	76.0
39	76.0	78.0
40	78.0	80.0



Specifications

Material

Insulator material:

Standard

Polyamide, Nylon 6T, UL 94V-0

Options:

Polymer, LCP, UL 94V-0

Polyester, PBT, UL 94V-0

Contact Terminal : Copper Alloy

Plating

See Ordering Grid

Electrical

Current Rating: 2 Amp per pin

Contact Resistance: 20 mΩ max.

Insulation Resistance: 1000 MΩ min.

Dielectric Withstand Voltage: 500 V AC

Mechanical & Environmental

Operating Temperature: -40°C to +105°C

Soldering process:

Nylon 6T (Standard) -

IR Reflow: 260°C for 10 sec.

Wave: 230°C for 5-10 sec.

Manual solder: 350°C for 3-5 sec

LCP (Option) -

IR Reflow: 260°C for 10 sec.

Wave: 250°C for 5-10 sec.

Manual solder: 350°C for 3-5 sec

PBT (Option) -

Manual Solder: 330°C for 3-5 sec

(Not Suitable for High Temperature Process)

Mates with (subject to pin length):

BF070 BF085 BF086 BF087 BF088 BF090

BF085 Recommended mating length 3.00mm

Ordering Grid

BF020-XX-X-X-XXXX-XXXX-X-X

No. of Contacts
02 to 40

Contact Plating

A = Gold Flash All Over (Standard)

B = Selective Gold Flash Contact Area/Tin On Tail

C = Tin All Over

G = 10μ" Gold Contact Area/Tin On Tail

I = 30μ" Gold Contact Area/Tin On Tail

Insulator Height 'H'

B = 2.00mm (Standard)

A = 1.50mm

Request Samples
and Quotation

Packing Options

G = Plastic Box (Standard)

D = Tube

E = Tube with Cap

Insulator Material

N = Nylon 6T (Standard)

P = PBT

L = LCP

Dimension D (1/100mm) (Tail Length)

0300 = 3.00mm (Standard)

Or specify Custom Tail Length

e.g. 2.50mm = 0250

(Maximum 1500 = 15.00mm)

(Minimum 0050 = 0.50mm)

Dimension C (1/100mm) (Post Height)

0300 = 3.00mm (Standard)

0400 = 4.00mm (Standard)

0600 = 6.00mm (Standard)

Or specify Custom Post Height

eg 0250 = 2.50mm

(Maximum 1500 = 15.00mm)

(Minimum 0050 = 0.50mm)

Part Number		Product Description	
BF020		2.00mm Pitch Pin Header	
Drawing Date		Single Row, Through Hole, Vertical	
25th October 2007			
By	CC	Tolerances (Except as Noted)	Units:
Detail	BF020 D PCN	Length X. ± 0.30 X.X ± 0.20 X.XX ± 0.15 X.XXX ± 0.10	Metric (mm)
Revision	D3	Angle X° ± 5° X.X° ± 2° X.XX° ± 1° X.XXX° ± 0.5°	3rd Angle Projection
Date	11/09/17		
		This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE	
		Not to Scale	Sheet No. 1/1

GCT
www.gct.co

Not to Scale
Drawn By LYH
Sheet No. 1/1