


MODEL NUMBER	Ø"A"	Ø"B"
CBBJRX79ZZ-G	.24	.063
CBBJRX79ZZA-G	.34	.070


REV	ECO	DATE
—	—	—
001	60038	2/26/2025
002	60386	2/20/2026









CBBJR79TL-G SHOWN




CBBJR79-G SHOWN




CBBJR79FL-G SHOWN



CBBJR79-G SHOWN



RECOMMENDED MTG
HOLE PATTERN



RECOMMENDED
PANEL CUTOUT


NOTES: UNLESS OTHERWISE SPECIFIED:

1. MATERIAL & FINISH:
   1.1 BODY: GOLD PLATED BRASS
   1.2 INSULATOR & DIELECTRIC: PTFE (TEFLON)
   1.3 INTERMEDIATE CONTACT: GOLD PLATED BRASS
   1.4 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
   1.5 MOUNTING HARDWARD: GOLD PLATED COPPER ALLOY

2. ELECTRICAL:
   2.1 FREQUENCY (MAX): 500 MHz
   2.2 IMPEDANCE: NON-CONSTANT

3. PANEL NUT TORQUE (MAX): 35 INCH POUNDS

4. PANEL THCKNESS (MAX): .125



CBBJR379A-G SHOWN

cinch CONNECTIVITY SOLUTIONS a bel group

NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.

INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018

Model No: CBBJRX79ZZB-G

RoHS2 ☑ 2015/863/EU

UNLESS OTHERWISE SPECIFIED UNITS: INCH
.XX ±.02
.XXX ±.010
ANGLES ±2°

Cage Code 14949

3RD ANGLE PROJECTION

ENGINEER: C.MONAHAN

Date: 2/20/2026

TROMPETER

Title: TRB RIGHT ANGLE JACK, CIRCUIT BOARD, GOLD

Drawing No. C_3-0376

REV. 001

Size A | DO NOT SCALE DRAWING | Workmanship Std: TFS-4 | Sheet 1 OF 1

Please read our datasheet & drawing disclaimer here.