





MODEL NUMBER	Ø"A"	Ø"B"
CBBJR79ZZ-G	.24	.063
CBBJR79ZZA-G	.34	.070




REV	ECO	DATE
001	60038	2/26/2025
002	60386	2/20/2026



CBBJR79TL-G SHOWN




CBBJR79-G SHOWN





CBBJR79FL-G SHOWN

TRB JACK INTERFACE
PER MIL-STD-348,
FIGURE 201-2



CBBJR79-G SHOWN



NOTES: UNLESS OTHERWISE SPECIFIED:

1. MATERIAL & FINISH:


- 1.1 BODY: GOLD PLATED BRASS
- 1.2 INSULATOR & DIELECTRIC: PTFE (TEFLON)
- 1.3 INTERMEDIATE CONTACT: GOLD PLATED BRASS
- 1.4 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
- 1.5 MOUNTING HARDWARE: GOLD PLATED COPPER ALLOY

2. ELECTRICAL:

- 2.1 FREQUENCY (MAX): 500 MHZ
- 2.2 IMPEDANCE: NON-CONSTANT

3. PANEL NUT TORQUE (MAX): 35 INCH POUNDS

4. PANEL THICKNESS (MAX): .125



CBBJR379A-G SHOWN

 cinch CONNECTIVITY SOLUTIONS a bell group NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018	Model No:		CBBJR79ZZB-G		TROMPETER														
	RoHS2 		2015/863/EU		Cage Code		14949		Title:		TRB RIGHT ANGLE JACK. CIRCUIT BOARD, GOLD								
	UNLESS OTHERWISE SPECIFIED UNITS: INCH				3RD ANGLE PROJECTION		ENGINEER:		C. MONAHAN		Drawing No.		C_3-0376	REV.	00				
	.XX ±.02 .XXX ±.010 ANGLES ±.02		Date:		2/20/2026		Size		A		DO NOT SCALE DRAWING		Workmanship Std:		TFS-4		Sheet		1 OF 1