








NOTA	SPECIFICATIONS
1	CONNECTEUR DOIT ETRE CONFORME AU CDC :96 238 404 99
2	CONNECTEUR SUIVANT: -CLASSE DE TEMPERATURE T3 SELON B217050 REV A -CLASSE DE VIBRATION MOTEUR SELON B217050 REV A -CLASSE ETANCHEITE 2 SELON B217050 REV A FEMALE CONNECTOR ACCORDING TO TEMPERATURE CLASS 3 ACCORDING TO B217050 REV A ENGINE VIBRATION CLASS ACCORDING TO B217050 REV A SEALING CLASS 2 ACCORDING TO B217050 REV A
3	PRECONISATION D'UTILISATION I USER MANUAL REF. MVL: PU 0211MVL'S REFERENCE: PU 027
4	ALVEOLE SUIVANT STE: 96 288 230 99 CAVITY ACCORDING TO: STE: 96 288 230 99
5	CONNECTEUR ET POSITION ALVEOLE CONFORMES AU PLAN D'INTERFACE 211FT0523 ET STE 96 339 622 99 FEMALE CONNECTOR AND CAVITY'S POSITION ACCORDING TO: DRAWING INTERFACE 211FT0523 ET STE 96 339 622 99
6	CONDUCTEUR SUIVANT STE : 96 418 794 99 WIRE ACCORDING TO: STE :96 418 794 99
7	CONDITIONNEMENT SUIVANT NORME: E73 03 150G PACKAGING ACCORDING TO STANDARD: E73 03 150G
8	DIAMETRE DE L'ISOLANT DES FILS WIRE INSULATION DIAMETER -MINI=1.40 -MAXI=2.80
9	MASSE DU PRODUIT LIVRABLE : 10g DELIVERY CONNECTOR WEIGHT : 10g
10	CHARNIERE DE PLAQUETTE ARRIERE ABSENTE OU CASSEE ADMISE MISSING OR BROKEN REAR PLATE HINGE ALLOWED
11	DEFAUTS D'ASPECT SUR ZONES NON FONCTIONNELLES ADMIS VISUAL DEFECTS ON NO FUNCTIONAL AREAS ALLOWED



PORTE-CLIPS FEMALE HOUSING	211 1 0 080	PBT NON CHARGE PBT: 0% GF	 27	NOIR BLACK
GRILLE TPA	211 M 4 131	PBT: 15% FV PBT: 15% GF	 28	JAUNE YELLOW
	211 M 6 131			BLEU BLUE
	211 M 8 131			GRIS GREY
GROMMET MAT SEAL	211 M 132	SILICONE 30Sh A	 29	VERT GREEN
JOINT INTERFACIAL INTERFACIAL SEAL	211 M 133	SILICONE 30Sh.A	 30	BLEU BLUE
DESIGNATION DESCRIPTION	REF. MVL MVL'S REFERENCE	MATIERE MATERIAL		COULEUR COLOUR






ECHELLE 1:1
SCALE 1:1

CODAGE NOIR REPRESENTE
BLACK CODING DRAW


			VUE F VIEW F TOLERANCES : ± 0.05 ECHELLE 3:2 SCALE: 3:2
JAUNE / YELLOW	BLEU 1 / BLUE	GRIS 1 / GREY	COULEUR GRILLE COLOUR TPA
NOIR 1 / BLACK	BLEU 2 / BLUE	GRIS 2 / GREY	CODAGE MECANIQUE SELON NF R 13-460 MECHANICAL CODING ACCORDING TO NF R 13-460
211 PC 05 2S 0 081	211 PC 05 2S 6 081	211 PC 05 2S 8 081	PART NUMBER
B	B	B	PART REVISION
10820113	33500308	10846260	PART NUMBER
01	01	01	PART REVISION

DELPHI P/N ADDED									
ECN-NO. WORK ORDER		POSITION	CHANGE DESCRIPTION MODIFICATION						
PRODUCT SPEC SPEC-PRODUCT1		PRODUCT SPEC SPEC-EMBRAGE	APPLICATION SPEC SPEC-APPLICATION		COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISION 10 THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE INFORMATION, DISSEMINATION OR UTILIZATION OF THIS DRAWING OR ITS RELATED DATA OR ANY DATA, AS WELL AS COMMUNICATION OF ANY CONTENT OR INFORMATION THEREOF, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED. IT IS FURTHER THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE INFORMATION, DISSEMINATION OR UTILIZATION OF THIS DRAWING OR ITS RELATED DATA OR ANY DATA, AS WELL AS COMMUNICATION OF ANY CONTENT OR INFORMATION THEREOF, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.				
TOLERANCES TOLERANCES		±0.1 ±2°	MATERIAL MATERIAL -		DELPHI				
CONTINENT #1 CONTINENT #1			SEE TABLE		DELPHI PARTIAL ELECTRICAL/ELECTRONIC ARCHITECTURE EPENOR, FRANCE				
DO NOT MEASURE DRAWING IN P/2 PRESENCE OF COOTS			SEE TABLE		C 130 PROJECTION 130 PROJECTION 130 PROJECTION				
DATE		NAME	DESIGNATION	COLOUR / COLOUR -	COOL BY: 644 COOL BY: 6	DRAWING NUMBER REF. PLAN			
2009-06-24		J. PERRIN	5-WAY 15 X08 FEMALE CONNECTOR			PCC0736946 C			
2009-06-24		F. FAUGIER	PROJECT PROJECT			SERIAL RELEASED C			
2009-06-24		S. LAFOITE	MINI SEALED "CS" FAMILY			See Table			
2009-06-24		Phonix MURARO	FR-216B (MURARO CAS 211 PC 65 2 X 5 X 8)						
2009-06-24		Phonix MURARO	NO MODIFICATION ALLOWED OUTSIDE DELPHI OR DELPHI'S CUSTOMERS						




NOTA	SPECIFICATIONS
1	CONNECTEUR SANS CPA SUIVANT: <i>VOIR NOTA FEUILLE N°1</i> FEMALE CONNECTOR WITHOUT CPA ACCORDING TO : <i>SEE NOTA SHEET N°1</i> CONNECTEUR : CPA SUIVANT PIV N° FEPS-09009 CONNECTOR WITH CPA FOLLOWING SPEC N° FEPS-09009
3	PRECONISATION D'UTILISATION IUSER MANUAL REF. MVL: PU 027/MVL'S REFERENCE: PU 027
4	CONDITIONNEMENT SUIVANT NORME: E73 03 150G PACKAGING ACCORDING TO STANDARD: E73 03 150G
5	MASSE DU PRODUIT (CONNECTEUR+CPA) LIVRABLE : 11g DELIVERY CONNECTOR(CONNECTOR+CPA) WEIGHT : 11g
6	DEFAUTS D'ASPECT SUR ZONES NON FONCTIONNELLES ADMIS VISUAL DEFECTS ON NO FUNCTIONAL AREAS ALLOWED



ISOLANT PORTE-CLIPS FEMALE HOUSING	211 1 0 080	PBT NON CHARGE PBT: 0% GF	NOIR BLACK
GRILLE TPA	211 M 4 131	PBT: 15% FV PBT: 15% GF	JAUNE YELLOW
	211 M 6 131		BLEU BLUE
	211 M 8 131		GRIS GREY
	GROMMET MAT SEAL		211 M 132
JOINT INTERFACIAL INTERFACIAL SEAL	211 M 133	SILICONE 30ShA	BLEU BLUE
CPA CPA	C 055500	PA 66 CHARGE 30% PA 66 30% GF	ORANGE ORANGE
DESIGNATION DESCRIPTION	REF. MVL MVL P/N	MATIERE MATERIAL	COULEUR COLOUR



SCALE 1:1
CODAGE NOIR REPRESENTÉ
BLACK CODING DRAWN

			VUE F VIEW F ECHELLE : 3:2 SCALE : 3:2
JAUNE / YELLOW	BLEU / BLUE	GRIS / GREY	COULEUR GRILLE TPA COLOUR
NOIR / BLACK	BLEU / BLUE	GRIS / GREY	CODAGE MECANIQUE SELON NF R 13-460 MECHANICAL CODING ACCORDING TO NF R 13-460
F 155500	F 655500	F 755500	PART NUMBER
B	B	B	PART REVISION
13798030	33502227	33502243	PART NUMBER
01	01	01	PART REVISION

[illegible]