


RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS 8mm

▲ SWITCH FUNCTION


POS. 1	POS. 2
ON	(ON)
1-3, 4-6	1-2, 4-5

(ON) = MOMENTARY




NOTE:




1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
5A 220VAC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 M Ω MIN.
8. DIELECTRIC STRENGTH: 1,500 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
10. OPERATING TEMP.: -40°C to 85°C
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. HARDWARE SUPPLIED: O-RING AND HEXNUT
13. INGRESS RATING: IP67
- ▲ 14. LAMP VOLTAGE: NO LAMP



▲ ACTUATOR
STAINLESS STEEL



▲ BODY
STAINLESS STEEL



M16 x 1.0



REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-104122	CORRECT TERMINAL BASE	05/21/26	JS



E-SWITCH®

OBJECT ID
100130680

TITLE PV16F2H0SS				
SCALE 3:2	DATE 7/17/2025	DR JS	DWG 52-PV16F2H0SS	REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED