

RVPX-J08EXX		DOCUMENT NO.
REV. A	SHEET 1 OF 2	
REVISIONS M		
LTR	DESCRIPTION	DATE
A	INITIAL RELEASE	11-FEB-16






TABLE 1


PLATING THICKNESS AND MATERIAL BY PART NUMBER			
PART NUMBER	GOLD IN CONTACT AREA	COMPLIANT	NICKEL OVERALL
RVPX-J08EM1	50 μ-INCH MIN	50 μ-INCH MIN TIN	50 μ-INCH MIN
RVPX-J08EM2	50 μ-INCH MIN	50 μ-INCH MIN TIN-LEAD	50 μ-INCH MIN
RVPX-J08EC1	30 μ-INCH MIN	50 μ-INCH MIN TIN	50 μ-INCH MIN
RVPX-J08EC2	30 μ-INCH MIN	50 μ-INCH MIN TIN-LEAD	50 μ-INCH MIN

- 4 ADDITIONAL CONNECTOR-SIDE KEEPOUT AREA REQUIRED IF CONNECTOR-SIDE EXTRACTION TOOL IS TO BE USED.
- 3 SEE TABLE 1 FOR PART NUMBER AND FINISHES
- 2 PTH CALLOUT TYPICAL HOLE
Ø0.63-.67 DRILL
Ø0.56 ±.05 FINISH HOLE
Ø1.02 PAD
- 1 HOUSING: GLASS FILLED LCP, UL94 - V0
CONTACT: Cu ALLOY




THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.		
DOCUMENT NO.	SHEET 1 OF 2	REV. A
RVPX-J08EXX		

PRO/ENGINEER INFORMATION	
Pro/e Model Used:	
RVPX-J08EXX.ASSEM	
Drawing Name:	
RVPX-J08EXX	

UNLESS OTHERWISE SPECIFIED	SPECIFICATIONS
LINEAR DIMENSIONS ARE IN MILLIMETERS TOLERANCES: .XXXX = ± ANGLES= ±2° .XXX = ± .XX = ±.1 .X = ±.13	MATERIAL SPEC. N/A
DIM.& TOL. PER ASME Y14.5M; DRM PER MIL-DTL-31000; OTHER Amphenol Sds. PER 9-3800	PROCESS SPEC. 9-3895 9-3856-5
LEGENDS: =FLAG NOTE CALL OUT REFERENCE ONLY	

POS		QTY	PART NUMBER	DESCRIPTION	NOTE
PARTS LIST					
APPROVALS		DATE	AMPHENOL CORPORATION		
PREPARED BY S. L'ANGELIER		22-SEP-15	40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838		
ENGINEER IN CHARGE S. L'ANGELIER			CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, 8 POS., LEFT END RVPX		
DESIGN MANAGER J. PAUL					
DESIGN ACTIVITY GROUP BOARD LEVEL					
THIRD ANGLE PROJECTION			SIZE C	CAGE CODE 77820	DOCUMENT NO. RVPX-J08EXX
			SCALE: 5.0	REF. NONE	REV. A
			SHEET 1 OF 2		

REAR TRANSITION MODULE APPLICATION



NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

RTM PC BOARD LAYOUT
(CONNECTOR SIDE)
SCALE 5/1

—PLASTIC ALIGNMENT PIN MUST BE
REMOVED FLUSH TO HOUSING BODY
PRIOR TO INSERTION INTO RTM LAYOUT