





RoHS Compliance



2P~6P Ribs on both sides
7P~24P No rib



REV.	SIGN	DATE	DESCRIPTION	APPROVER
B	/	6/15/22	The first release	Jonhson

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ④ Terminal lever: Thermoplastic (UL94V-0) Orange(RAL 2011/P)
 - Item ⑤ Terminal top housing: Thermoplastic (UL94V-0)
 - Item ③ Female contact : PhBz Bright Tin Plated.
 - Item ① Spring clamp : Stainless steel
 - Item ② Terminal down housing: Thermoplastic (UL94V-0)
- Electrical: cULus
- Voltage rating: 160 V
 - Current rating: 5.5 A
 - Wire range:
 - Solid wire(AWG): 16-24
 - Stranded wire(AWG): 16-24
 - Wire strip length: 9-10 mm
 - Withstanding Voltage: 1.32 KV
 - Operating temperature: -40°C to +115°C
 - APPROVAL:
 - Critical dimension: ▲

KD xx 1 0 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
:
24: 24 POLES

Body COLOR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange (RAL2011/P)
4 Yellow (RAL1018/A)
5 Green(RAL6018/T)
6 Blue(RAL 5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)

RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

$$\text{DimL}=(N-1)\times 3.5+4.2$$

$$\text{DimP}=(N-1)\times 3.5$$

N=Number of poles

POLES	Dim. Tol	Dim.L/P
2p-6p		±0.15
7p-12p		±0.25
13p-18p		±0.30
19p-24p		±0.40

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KD 3.5mm W/O Flange Series				
PART NO.	KDxx10x0xxxxG			DWG NO.	8KD0073
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Johnson 2022.06.15	Johnson 2022.06.15		X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
SHEET: 01/01				UNIT: mm SCALE: NONE REV.: B	