

RVPX-J16EXX		
DOCUMENT NO. 100		
REVISIONS		
LTR	DESCRIPTION	DATE
A	INITIAL RELEASE	11-FEB-16





TABLE 1

PLATING THICKNESS AND MATERIAL BY PART NUMBER			
PART NUMBER	GOLD IN CONTACT AREA	COMPLIANT	NICKEL OVERALL
RV PX-J16 EM1	50 µ-INCH MIN	50 µ-INCH MIN TIN	50 µ-INCH MIN
RV PX-J16 EM2	50 µ-INCH MIN	50 µ-INCH MIN TIN-LEAD	50 µ-INCH MIN
RV PX-J16 EC1	30 µ-INCH MIN	50 µ-INCH MIN TIN	50 µ-INCH MIN
RV PX-J16 EC2	30 µ-INCH MIN	50 µ-INCH MIN TIN-LEAD	50 µ-INCH MIN





- 4 ADDITIONAL CONNECTOR-SIDE KEEPOUT AREA REQUIRED IF CONNECTOR-SIDE EXTRACTION TOOL IS TO BE USED.
- 3 SEE TABLE 1 FOR PART NUMBER AND FINISHES
- 2 PTH CALLOUT TYPICAL HOLE
Ø0.63-.67 DRILL
Ø0.56 ±.05 FINISH HOLE
Ø1.02 PAD
- 1 HOUSING: GLASS FILLED LCP, UL94 - V0
CONTACT: Cu ALLOY

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.		
DOCUMENT NO.	SHEET 1 OF 2	REV. A
RVPX-J16EXX		

PRO/ENGINEER INFORMATION	
Pro/e Model Used:	N/A
RV PX-J16 EXX PART	
Drawing Name:	NEXT ASSEMBLY
RV PX-J16 EXX	

UNLESS OTHERWISE SPECIFIED		SPECIFICATIONS		POS	QTY	PART NUMBER	DESCRIPTION	NOTE
LINEAR DIMENSIONS ARE IN MILLIMETERS TOLERANCES: .XXXX = ±. - ANGLES= ±1° .XXX = ±. - .XX = ±.13 .X = ±.5 DIM.& TOL. PER ASME Y14.5M; DRM PER MIL-DTL-31000; OTHER Amphenol Sids. PER 9-3800 LEGENDS: =FLAG NOTE CALL OUT REFERENCE ONLY		MATERIAL SPEC.		PARTS LIST				
		N/A		APPROVALS				
		PROCESS SPEC.		DATE				
		9-3895 9-3856-5		THIRD ANGLE PROJECTION				
				AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, NY. 13858				
				CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, 16 POS., RIGHT END RV PX				
				SIZE C CAGE CODE 77820 DOCUMENT NO. RV PX-J16 EXX REV. A				
				SCALE: 4.0 REF. SHEET 1 OF 2				

REAR TRANSITION MODULE APPLICATION



NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

RTM PC BOARD LAYOUT
(CONNECTOR SIDE)
SCALE 5/1

SIZE C	CAGE CODE 77820	DOCUMENT NO. RVPX-J16EXX	REV. A
SCALE: 4.0		REF:	SHEET 2 OF 2

DOCUMENT NO.
RVPX-J16EXX

SHEET 2 OF 2

REV

A

EV

1

1

1

1

1

TABLE 1

1

1000

1