







4

3

2

REV.	SHEET 1 OF 1	DOCUMENT NO. RVPX-HMD-X
REVISIONS M		
LTR	DESCRIPTION	DATE
A	INITIAL RELEASE	

TABLE 1	
PART NUMBER	DIM "A"
RVPX-HMD-1	0°
RVPX-HMD-2	45°
RVPX-HMD-3	90°
RVPX-HMD-7	270°
RVPX-HMD-8	315°
RVPX-HMD-9	NO KEY



- 7 GUIDE MODULE W/O KEYING
GUIDE PIN RVPX-HPD-X SERIES MUST BE ORIENTED
TO PROVIDE PROPER ESD PERFORMANCE
- 6 CONTACT FINISH: 3.81µm MINIMUM SILVER IN CONTACT AREA
OVER 1.27µm MINIMUM NICKEL ALL OVER
- 5 FINISH: SILVER OVER NICKEL OVER COPPER
- 4 GROUND PAD Ø5mm ON BOTH SIDE OF PCB
- 3 SEE TABLE 1 FOR KEY ORIENTATION
(P/N RVPX-HMD2 SHOWN ON DRAWING)
- 2 HOLE FOR POSTIVE RETENTION SCREW.
- 1 MATERIAL: HOUSING: ZINC ALLOY DIE CASTING
ZAMAK 3.
CONTACT: COPPER 7025

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

RELEASED / Jul . 06 2016, 11:10:43 AM

DOCUMENT NO. RVPX-HMD-X


SHEET 1 OF 1

REV. A

NONE

NEXT ASSEMBLY

PRO/ENGINEER INFORMATION
Pro/e Model Used:
RVPX-HMD-XM.ASSEM
Drawing Name:
RVPX-HMD-X

UNLESS OTHERWISE SPECIFIED		SPECIFICATIONS		POS	QTY	PART NUMBER		DESCRIPTION		NOTE			
LINEAR DIMENSIONS ARE IN MILLIMETERS TOLERANCES: .XXXX = ±. - ANGLES= ±1° .XXX = ±. - .XX = ±.13 .X = ±.5 ----- DIM. & TOL. PER ASME Y14.5M; DRM PER MIL-DTL-31000; OTHER Amphenol Stds. PER 9-3800 LEGENDS: -FLAG NOTE CALL OUT REFERENCE ONLY 		MATERIAL SPEC.		APPROVALS		DATE		AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838					
		SEE NOTE 1		PREPARED BY H. BROOKER		1-Jul-16							
				ENGINEER IN CHARGE S. L'ANGELIER									
				DESIGN MANAGER J. PAUL									
				PROCESS SPEC.				DESIGN ACTIVITY GROUP BOARD LEVEL		RVPX DAUGHTERCARD GUIDE DIECAST			
SEE NOTE 5		THIRD ANGLE PROJECTION											
						SIZE C		CAGE CODE 77820		DOCUMENT NO. RVPX-HMD-X		REV. A	
								SCALE: 4.0		REF. RVPX-HMDX		SHEET 1 OF 1	

3

2

1

D

C

0

A

Eng PDM Information
For Reference Only

REV. A

SHEET 1 OF 1

DOCUMENT NO. RVPX-HMD-X

U