



ELECTRICAL SPECIFICATIONS

FREQUENCY RANGE	5650 TO 7150 MHz
RETURN LOSS	-19 dB MAX
INSERTION LOSS	0.5 dB MAX
ISOLATION	-18 dB MAX
IMD3 (dBc) @ +33 dBm POUT	-65 dBc MAX
FORWARD POWER	20 W MAX
REVERSE POWER	10 W MAX
OPERATING TEMPERATURE RANGE	-40 TO +85 °C
STORAGE TEMPERATURE RANGE	-45 TO +85 °C
DIRECTION	CW

MATERIAL SPECIFICATIONS :

BODY MATERIAL : STEEL, SILVER PLATED
PIN : COPPER, GOLD PLATED

NOTES :

- 1.STANDARD INPUT/OUTPUT IMPEDANCE 50 Ohm.
- 2.LEAD FREE, NO Nd MATERIAL, BeO FREE.
- 3.THE DIMENSION OF DATA MATRIX IS 3.0X3.0MM INFORMATION INCLUDING WORK ORDER NUMBER-SERIAL NUMBER-MATERIAL NUMBER
- 4.THIS PART COMPLIES WITH ALL RoHS REQUIREMENTS

ENG PART#: 801-565-715-PT040

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
FUNCTIONAL SYMBOLS	DIMENSION UNITS	SCALE	CURRENT REV DESC:						
$F_A=0$	MM	1:1	CHANGE ECTR RESTRICTED ***						
$F_P=0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 702316						
$F_D=0$	mm INCH		DRWN: SREN05 2022/04/20						
DIVISIONAL SYMBOLS	4 PLACES	±0.005 ±----	CHK'D: WWANG99 2022/04/21						
	3 PLACES	±0.025 ±----	APPR: HWANG186 2022/04/22						
	2 PLACES	±0.13 ±----	INITIAL REVISION:						
	1 PLACE	±0.25 ±----	DRWN: SREN05 2021/12/08						
	0 PLACES	±0.4 ±----	APPR: HWANG186 2022/03/01						
	ANGULAR TOL ± 1.5 °		DOCUMENT NUMBER						
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			A3-SIZE		73591	0735912081	GENERAL MARKET	PSD 000	A1