



RECOMMENDED LAND PATTERN :
 Zone A must be attached to heat sink. Thermal conductivity of intermediate layers between Zone A and heat sink must be better than 0.1 W / [°C x mm].

ELECTRICAL SPECIFICATION :
 Frequency Range : 717 to 756 MHz
 Input power : 100 W
 Input power , peak : 1300 W
 Reflected power : 80 W
 Isolation : 22 dB Min
 Return Loss (Measured at port 1 and port 2) : 23 dB Min (0°C-115°C)
 (Measured at port 1 and port 2) : 20 dB Min (-40°C-0°C)
 Insertion loss (within frequency range, port 1 to 2) : 0.25 dB Max
 Intermodulation distortion, IM3(2 x 50 W) : -65 dBc Max
 IM5(2 x 50 W) : -79 dBc Max
 Harmonics: 2 x f(100W CW) : 0dBm Max
 3-4 x f (100W CW) : -10dBm Max
 5 x f (100W CW) : -35dBm Max
 6-7 x f (100W CW) : -25dBm Max
 Operating temperature range : -40°C to +115°C
 Storage temperature range : -40°C to +125°C
 Direction : CCW

BODY: CARBON STEEL, SILVER PLATED
RIGID PINS: COPPER, SILVER PLATED
NOTES:
 1.STANDARD INPUT/OUTPUT IMPEDANCE 50 Ohm
 2.LEAD FREE, NO Nd MATERIAL, BeO FREE
 3.THE DIMENSION OF DATE MATRIX IS 7.6X7.6MM INFORMATION INCLUDING WORK ORDER NUMBER-SERIAL NUMBER-MATERIAL NUMBER
 4.THIS PART COMPLIES WITH ALL RoHS REQUIREMENTS

ENG PN#: 811-071-076-WB040

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
	DIMENSION UNITS	SCALE	CURRENT REV DESC:			
$F_A=0$	MM	1:1	CHANGE ECTR RESTRICTED ***	EC NO: 702316		
$F_E=0$	GENERAL TOLERANCES (UNLESS SPECIFIED)			DRWN: SREN05	2022/04/20	
$F_P=0$		mm	INCH	CHK'D: WWANG99	2022/04/21	
DIVISIONAL SYMBOLS	4 PLACES	±0.005	±----	APPR: HWANG186	2022/04/22	
	3 PLACES	±0.025	±----	INITIAL REVISION:		
	2 PLACES	±0.13	±----	DRWN: SREN05	2021/12/09	
	1 PLACE	±0.25	±----	APPR: HWANG186	2022/03/01	
	0 PLACES	±0.4	±----	DOCUMENT NUMBER		
	ANGULAR TOL ± 1.5 °				735912094	PSD 000 A1
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER
			A3-SIZE	73591	0735912094	GENERAL MARKET
						SHEET NUMBER
						1 OF 1