


LOOSE PIECE BOX		TAPE MOUNTED PARTS		STUD SIZE	∅S	∅W ±.012/0.30	L MAX	C MIN	T REF	H ±.02/0.5
MAT'L NO.	ENG NO.	MAT'L NO.	ENG NO.							
190710134	D-650-08X	190710135	D-650-08XT	8	.173/4.39	.468/11.89	1.31/33.3	.363/9.22	.045/1.14	1.070/27.18
190710136	D-650-10X	190710139	D-650-10XT	10	.198/5.03	.468/11.89	1.31/33.3	.363/9.22	.045/1.14	1.070/27.18
190710140	D-650-14X	190710143	D-650-14XT	1/4	.265/6.73	.468/11.89	1.31/33.3	.363/9.22	.045/1.14	1.070/27.18
190710144	D-650-56X	190710145	D-650-56XT	5/16	.328/8.33	.468/11.89	1.31/33.3	.363/9.22	.045/1.14	1.070/27.18
190710146	D-651-10X	-	-	10	.198/5.03	.583/14.81	1.43/36.3	.428/10.87	.045/1.14	-
190710148	D-651-14X	190710149	D-651-14XT	1/4	.265/6.73	.583/14.81	1.43/36.3	.428/10.87	.045/1.14	1.070/27.18
190710153	D-651-56X	190710155	D-651-56XT	5/16	.328/8.33	.583/14.81	1.43/36.3	.428/10.87	.045/1.14	1.070/27.18
190710150	D-651-38X	190710152	D-651-38XT	3/8	.390/9.91	.583/14.81	1.43/36.3	.428/10.87	.045/1.14	1.070/27.18
-	-	190710160	D-652-12XT	1/2	.515/13.08	.810/20.57	1.73/43.9	.611/15.52	.050/1.27	1.400/35.56
190710172	D-653-56X	-	-	5/16	.328/8.33	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-
190710171	D-653-38X	-	-	3/8	.390/9.91	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-
190710174	D-653-76X	-	-	7/16	.453/11.51	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-
190710173	D-653-58X	-	-	5/8	.656/16.66	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-
190710176	D-656-06X	190710177	D-656-06XT	6	.146/3.71	.374/9.50	1.27/32.3	.363/9.22	.045/1.14	1.070/27.18
190710178	D-656-08X	190710179	D-656-08XT	8	.173/4.39	.374/9.50	1.27/32.3	.363/9.22	.045/1.14	1.070/27.18
190710180	D-656-10X	190710181	D-656-10XT	10	.198/5.03	.374/9.50	1.27/32.3	.363/9.22	.045/1.14	1.070/27.18
190710182	D-656-14X	190710184	D-656-14XT	1/4	.265/6.73	.374/9.50	1.27/32.3	.363/9.22	.045/1.14	1.070/27.18







PARTS ON TAPE
(DOUBLE SPACED)

NOTES:
1. MATERIALS:
   TERMINAL: TIN-PLATED COPPER
   INSULATION: RED PVC
2. PARTS ARE RoHS COMPLIANT.
3. MWID = MAXIMUM WIRE INSULATION DIAMETER.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
INCH/mm	1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	± 0.02
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: REMOVED OBSOLETED PART NUMBERS AS PER PCN#5114356.

EC NO: 803783
DRWN: RAVINR1 2024/11/06
CHK'D: GGA 2024/11/19
APPR: GGA 2024/11/19

INITIAL REVISION:
DRWN: RFC_PLMIMP 2019/03/22
APPR: jmacneil 2007/09/19

THIRD ANGLE PROJECTION | DRAWING: C-SIZE | SERIES: 19071

molex

RING TONGUE TERMINALS
8 AWG INSULKRIMP

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-19071-002	PSD	001	C2

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2024/11/19 08:37:16

FORMAT: Eng-lega-master-lb-prod-C
REVISION: E1
DATE: 2021/05/01