





- NOTES:
- MATERIALS:
TERMINAL: TIN-PLATED COPPER
INSULATION: RED PVC
 - PARTS ARE RoHS COMPLIANT.
 - MWID = MAXIMUM WIRE INSULATION DIAMETER.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

INCH/MM

SCALE

NTS

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

CURRENT REV DESC: REMOVED OBSOLETE PART
NUMBERS AS PER PCN#514317

EC NO: 804310

DRWN: VISHAH2

CHK'D: GGA

APPR: GGA

2024/11/14

2024/11/22

2024/11/22

INITIAL REVISION:

DRWN: ABENJAMINLW

APPR: JMACNEIL

2019/07/10

2019/08/06

mo

lex

RING TONGUE TERMINAL
2 AWG INSULKRIMP

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

190710272

DOC TYPE

PSD

DOC PART

000

REVISION

A2

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

1 OF 1

THIRD ANGLE PROJECTION

DRAWING

C-SIZE

SERIES

19071

12

11

10

9

8

7

6

5

4

3

2

1

DOCUMENT STATUS

P1

RELEASE DATE

2024/11/22

10:34:52

FORMAT: English-Metric-20-anno-C

REVISION: E1

DATE: 2024/09/01