



12	11	10	9	8	7	6	5	4	3	2	1
LOOSE PIECE		TAPE MOUNTED		SPECIFICATIONS							
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.	"H"		
192030156	C-T-328-08	192030098	C-T-328-08T	8	.173 [4.39]	.375 [9.53]	.303 [7.70]	.785 [19.94]	1.234 [31.34]		
192030099	C-T-328-10	192030100	C-T-328-10T	10	.198 [5.03]						
192030182	C-T-330-14	192030101	C-T-330-14T	14	.265 [6.73]	.530 [13.46]	.393 [9.98]	.952 [24.18]	1.234 [31.34]		



PARTS ON TAPE

- NOTES:
- 1. MATERIAL: COPPER (STOCK THICKNESS .040±.001 [1.02])
PLATING: WATTS BATH NICKLE (.0002 MIN)
 - 2. BRAZED SEAM
 - 3. WIRE SIZE: 12 - 10 AWG
4.0 - 6.0 MM²
 - 4. MAX. OPERATING TEMP : 650 °F
343 °C
 - 5. "UL" LISTING #E32244
"CSA" LISTING #18689
 - 6. ALL DIMENSIONS IN INCHES/[MM].
 - 7. PARTS ARE ROHS COMPLIANT.
 - 8. DIMS. SHOWN ARE FOR REFERENCE ONLY.

DOCUMENT STATUS	P1	RELEASE DATE	2024/05/13	16:21:59
-----------------	----	--------------	------------	----------

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE	
INCH/mm	NTS	
GENERAL TOLERANCES (UNLESS SPECIFIED)		
	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#513405

EC NO: 784316
DRWN: MADHAM5
CHK'D: GGA
APPR: GGA

2024/04/17
2024/05/13
2024/05/13

INITIAL REVISION:
DRWN: JJ
APPR: JMACNEIL

1984/11/28
2019/08/05

mo

le

x

RING TONGUE TEMP-TERMINAL
650 °F MAX VERSAKRIMP

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
192030156	PSD	000	A1

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 1

THIRD ANGLE PROJECTION

DRAWING

SERIES

C-SIZE

19203