


10	9		8		7		6		5		4		3		2		1	
MAT'L NO (LOOSE PC)	ENG NO (LOOSE PC)	MAT'L NO (ON STRIP)	ENG NO (ON STRIP)	MAT'L NO (ON TAPE)	ENG NO (ON TAPE)	WIRE GAGE	FITS MALE TAB		COLOR	"A" MAX	Ø"B" MIN	"C" MAX	MWID	"E" MAX	"H" REF			
190030071	M-2212	190030106	M-2212C	190030073	M-2212T	26-24	.250 x .032 (6.35 x 0.81)		YELLOW	.86 (21.8)	.028 (0.71)	.38 (9.7)	.075 (1.91)	.18 (4.6)	1.42 (36.1)			
190030064	M-2210	190030103	M-2210C	190030067	M-2210T		.187 x .020 (4.75 x 0.51)		YELLOW	.78 (19.8)		.32 (8.1)		.16 (4.1)	1.38 (35.1)			
190030068	M-2211	190030104	M-2211C	190030070	M-2211T		.187 x .032 (4.75 x 0.81)		DK YELLOW									
190030001	AA-2201	190030105	AA-2201C	190030003	AA-2201T	22-18	.250 x .032 (6.35 x 0.81)		SALMON	.86 (21.8)	.056 (1.42)	.38 (9.7)	.135 (3.43)	.18 (4.6)	1.42 (36.1)			
190030036	AA-2213	190030109	AA-2213C	190030074	AA-2213T		.205 x .020 (5.21 x 0.51)		SALMON	.78 (19.8)				.32 (8.1)	.16 (4.1)	1.38 (35.1)		
190030038	AA-2214	190030110	AA-2214C	190030075	AA-2214T		.205 x .032 (5.21 x 0.81)		PINK									
190030011	AA-2202	190030107	AA-2202C	190030013	AA-2202T		.187 x .020 (4.75 x 0.51)		SALMON									
190030017	AA-2203	190030108	AA-2203C	190030020	AA-2203T		.187 x .032 (4.75 x 0.81)		PINK									
190030024	AA-2204	190030097	AA-2204C	190030026	AA-2204T		.110 x .020 (2.79 x 0.51)		SALMON									
190030030	AA-2205	190030098	AA-2205C	190030032	AA-2205T		.110 x .032 (2.79 x 0.81)		PINK									
190030040*	BB-2206	190030041*	BB-2206C	190030042*	BB-2206T	16-14	.250 x .032 (6.35 x 0.81)		BLUE	.86 (21.8)	.079 (2.01)	.38 (9.7)	.160 (4.06)	.18 (4.6)	1.41 (35.8)			
190030062*	BB-2215	190030085*	BB-2215C	190030077*	BB-2215T		.205 x .020 (5.21 x 0.51)		BLUE	.78 (19.8)				.32 (8.1)		.17 (4.3)		
190030063*	BB-2216	190030086*	BB-2216C	190030078*	BB-2216T		.205 x .032 (5.21 x 0.81)		AQUA									
190030050*	BB-2207	190030051*	BB-2207C	190030052*	BB-2207T		.187 x .020 (4.75 x 0.51)		BLUE									
190030056*	BB-2208	190030057*	BB-2208C	190030058*	BB-2208T		.187 x .032 (4.75 x 0.81)		AQUA									
196060002	C-2293	196060001	C-2293C	196060003	C-2293T	12-10	.250 x .032 (6.35 x 0.81)		YELLOW	1.03 (26.2)	.117 (2.97)	.38 (9.7)	.235 (5.97)	.22 (5.6)	1.53 (38.9)			



NOTE(S):

- MATERIAL:
TERMINAL: TIN PLATED BRASS
FERRULE: TIN PLATED BRASS
INSULATION: NYLON 6/6 94V-2, SEE CHART FOR COLOR.
- MWID = MAXIMUM WIRE INSULATION DIAMETER.
- MUST BE RoHS COMPLIANT.

4 THIN MEMBRANE MAY BE PRESENT IN TAB CUT-OUT.

DOCUMENT STATUS

P1

RELEASE DATE

2026/01/14

15:13:24

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
F/A = 0	DIMENSION UNITS	SCALE
	INCH/MM	NTS
F/E = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)	
		MM INCH
F/D = 0	4 PLACES	±
	3 PLACES	±
DIVISIONAL SYMBOLS	2 PLACES	±
	1 PLACE	±
	0 PLACES	±
	ANGULAR TOL	± °
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION
		DRAWING
		SERIES
		MATERIAL NUMBER
		CUSTOMER
		SHEET NUMBER

EC NO: 844661

DRWN: DEANNM1

CHK'D: ETHRODAHL

APPR: ETHRODAHL

INITIAL REVISION:

DRWN: BENDERLE

APPR: RDEROSS

2026/01/12

2026/01/14

2026/01/14

2002/04/02

2002/04/03

SD-19003-005

PSD

001

G2

SEE CHART

GENERAL MARKET

1 OF 1

DOCUMENT STATUS

P1

RELEASE DATE

2026/01/14

15:13:24