


FEMALE PLUG M8 90° ANGLED TO MALE PLUG M8 STRAIGHT



CONTACTS POSITION FRONT VIEW:

	3 CONTACTS		4 CONTACTS		5 CONTACTS	
	PIN	WIRE	PIN	WIRE	PIN	WIRE
FEMALE	1	BROWN	1	BROWN	1	BROWN
	3	BLUE	2	WHITE	2	WHITE
	4	BLACK	3	BLUE	3	BLUE
			4	BLACK	4	BLACK
MALE	1	BROWN	1	BROWN	1	BROWN
	3	BLUE	2	WHITE	2	WHITE
	4	BLACK	3	BLUE	3	BLUE
			4	BLACK	4	BLACK
CONNECTIONS	1	BROWN	1	BROWN	1	BROWN
	3	BLUE	2	WHITE	2	WHITE
	4	BLACK	3	BLUE	3	BLUE
			4	BLACK	4	BLACK
CODING ACCORDING TO IEC 61076-2-104						

NOTES:
RATED VOLTAGE: 3 contacts 60V AC/DC
4 and 5 contacts 30V AC/DC
CURRENT RATING: 3, 4, 5 contacts 3A
PROTECTION CLASS: IP 67
TEMPERATURE: -25°C / +80°C

FOR OPTIONS SEE - NUMERICAL CODE - ON SHEET 2

11	1	INSERT MALE BLACK	TPU	---
10	3 / 4 / 5	CONTACT M8 MALE	BRASS	SELECTIVE Au OVER Ni
9	1	SLEEVE	BRASS	NICKEL
8	1	COUPLING NUT M8 MALE	BRASS	NICKEL
7	1	LABEL YELLOW	VINYL	---
6	-	PRINTING FOR CABLES lxx	---	---
5	-	CABLE	SEE SHEET 2	---
4	1	OVERMOULDING BLACK	TPU	---
3	1	COUPLING NUT M8 FEMALE	BRASS	NICKEL
2	1	INSERT FEMALE BLACK	TPU	---
1	3 / 4 / 5	O-RING RED	FKM	---
1	3 / 4 / 5	CONTACT M8 FEMALE	BRASS	SELECTIVE Au OVER Ni
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	SCALE	CURRENT REV DESC: NEW PN ADDED	molex		
▽ = 0	mm	2:1	EC NO: 710179	CSE M8 M8 XP AC BC FE RA MA STR XM		
▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: ARPITT 2022/06/13	PRODUCT CUSTOMER DRAWING		
▽ = 0	ANGULAR TOL ± 1.0°		CHK'D: FDAFERNER 2022/06/15	DOCUMENT NUMBER		
▽ = 0	4 PLACES ±		APPR: FDAFERNER 2022/06/15	1200878243		
▽ = 0	3 PLACES ±		INITIAL REVISION:	PSD 000 A4		
▽ = 0	2 PLACES ± 0.05		DRWN: JMARSZALEK 2016/10/20	SHEET NUMBER		
▽ = 0	1 PLACE ± 0.3		APPR: RSILLER 2017/01/11	1 OF 3		
▽ = 0	0 PLACES ± 0.5		THIRD ANGLE PROJECTION	MATERIAL NUMBER		
▽ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING	CUSTOMER		
▽ = 0			A3-SIZE	GENERAL MARKET		
▽ = 0			SERIES	120087		
▽ = 0				SEE PART LIST		

10		9		8		7		6		5		4		3		2		1			
PART LIST																					
F	No.	Molex PN	Engineering No.	Cable Length	No.	Molex PN	Engineering No.	Cable Length	No.	Molex PN	Engineering No.	Cable Length	No.	Molex PN	Engineering No.	Cable Length					
	1	1200280016	443031E02M010	1m	36	1200878367	444031E02M030	3m	71				106								
	2	1200281220	443031P82M003	0.3m	37	1200878368	444031E02M050	5m	72				107								
	3	1200281221	443031P82M006	0.6m	38	1200878369	444031E02M100	10m	73				108								
	4	1200281283	443031E02M005	0.5m	39	1200878370	444031P02M003	0.3m	74				109								
E	5	1200875016	443031E02M006	0.6m	40	1200878371	444031P02M006	0.6m	75				110								
	6	1200878128	443031H08M020	2m	41	1200878372	444031P02M010	1m	76				111								
	7	1200878129	443031H08M030	3m	42	1200878373	444031P02M030	3m	77				112								
	8	1200878130	443031H08M050	5m	43	1200878499	443031H08M010	1m	78				113								
	9	1200878196	444031H08M010	1m	44	1200878542	443031E02M015Y	1.5m	79				114								
D	10	1200878197	444031P02M020	2m	45	1200878554	444031H08M006	0.6m	80				115								
	11	1200878242	445031E02M006	0.6m	46	1200878555	444031H08M020	2m	81				116								
	12	1200878243	445031E02M030	3m	47	1200878556	444031H08M050	5m	82				117								
	13	1200878244	445031E02M050	5m	48	1200878557	443031H08M006	0.6m	83				118								
	14	1200878254	444031P02M050	5m	49	1200878595	443031P02M010H	1m	84				119								
C	15	1200878303	443031E02M003	0.3m	50	1200878625	443031P82M050	5m	85				120								
	16	1200878304	443031E02M015	1.5m	51	1200878637	443031E02M002	0.2m	86				121								
	17	1200878305	443031E02M020	2m	52	1200878638	443031E02M025	2.5m	87				122								
	18	1200878306	443031E02M030	3m	53	1200878639	443031E02M065	6.5m	88				123								
	19	1200878307	443031E02M035	3.5m	54	1200878659	443031E02M010H	1m	89				124								
B	20	1200878308	443031E02M050	5m	55</																

No.	Molex PN	Engineering No.	Cable Length
36	1200878367	444031E02M030	3m
37	1200878368	444031E02M050	5m
38	1200878369	444031E02M100	10m
39	1200878370	444031P02M003	0.3m
40	1200878371	444031P02M006	0.6m
41	1200878372	444031P02M010	1m
42	1200878373	444031P02M030	3m
43	1200878499	443031H08M010	1m
44	1200878542	443031E02M015Y	1.5m
45	1200878554	444031H08M006	0.6m
46	1200878555	444031H08M020	2m
47	1200878556	444031H08M050	5m
48	1200878557	443031H08M006	0.6m
49	1200878595	443031P02M010H	1m
50	1200878625	443031P82M050	5m
51	1200878637	443031E02M002	0.2m
52	1200878638	443031E02M025	2.5m
53	1200878639	443031E02M065	6.5m
54	1200878659	443031E02M010H	1m
55	1200878660	443031E02M005H	0.5m
56	1200878664	443031E02M020H	2m
57	1200878667	444031E02M003H	0.3m
58	1200878672	443031E02M002H	0.2m
59	1200878673	443031E02M025H	2.5m
60	1200878674	443031E02M065H	6.5m
61	1200878690	443031E02M015H	1.5m
62	1200878942	445031H08M006	0.6m
63	1200878943	445031H08M010	1m
64	1200878944	445031H08M020	2m
65	1200878945	445031H08M050	5m
66	1200878948	445031E02M010	1m
67	1200878949	445031E02M020	2m
68	1200280400	444031P02M020	2m
69	1200878979	444031H08M030	3m
70	1200878981	445031H08M030	3m

No.	Molex PN	Engineering No.	Cable Length
106			
107			
108			
109			
110			
111			
112			
113			
114			
115			
116			
117			
118			
119			
120			
121			
122			
123			
124			
125			
126			
127			
128			
129			
130			
131			
132			
133			
134			
135			
136			
137			
138			
139			
140			

FORMAT: master-tb-mod-A3
REVISION: H 10

FORMAT: master-tb-mod-A3
REVISION: H 10