


10	9		8		7		6		5		4		3		2	1
MAT'L NO (LOOSE PC)	ENG NO (LOOSE PC)	MAT'L NO (ON TAPE)	ENG NO (ON TAPE)	INSUL COLOR	WIRE GAGE	Ø"A" MIN	STRIPE COLOR	WIRE GAGE	Ø"B" MIN	ØMWID	"L" MAX	Ø"OD" MAX	"H" REF			
191540022	BA-631X	191540057	BA-631XT	BLUE	16-14	.088 (2.24)	RED	22-18	.065 (1.65)	.170 (4.32)	1.10 (27.9)	.27 (6.9)	1.50 (38.1)			
191540035	CB-646X	191540036	CB-646XT	YELLOW	12-10	.137 (3.48)	BLUE	16-14	.091 (2.31)	.260 (6.60)	1.31 (33.3)	.36 (9.1)	1.70 (43.2)			
191540044	DC-654X	-	-	RED	8	.165 (4.19)	YELLOW	12-10	.138 (3.51)	.330 (8.38)	1.56 (39.6)	.43 (10.9)	-			
191540047	ED-662X	-	-	BLUE	6	.222 (5.64)	RED	8	.175 (4.45)	.430 (10.92)	1.88 (47.8)	.53 (13.5)	-			



- NOTES:
- 1. MATERIALS: PVC INSULATION OVER TIN-PLATED COPPER SPLICE.
COLOR: SEE CHART.
 - 2 MWID = MAXIMUM WIRE INSULATION DIAMETER.
 - 3. MUST BE RoHS COMPLIANT.

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
	DIMENSION UNITS	SCALE		CURRENT REV DESC: 191540022 MWID WAS .160			
		INCH/MM	NTS				
	GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 852381 DRWN: DEANNM1 2026/04/03 CHK'D: ETHRODAHL 2026/04/09 APPR: ETHRODAHL 2026/04/09 INITIAL REVISION: DRWN: RCM 1991/10/28 APPR: JMACNEIL 2011/04/27			
		MM	INCH				
DIVISIONAL SYMBOLS	4 PLACES	±	±	PRODUCT CUSTOMER DRAWING			
	3 PLACES	±	±				
	2 PLACES	±	±				
	1 PLACE	±	±				
	0 PLACES	±	±				
	ANGULAR TOL	±	°				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION	DRAWING	SERIES	
					B-SIZE	19154	
				MATERIAL NUMBER		CUSTOMER	
				SD-19154-007		GENERAL MARKET	
				DOC TYPE	DOC PART	REVISION	
				PSD	001	A6	
				SHEET NUMBER		1 OF 1	