






DETAIL OF MOUNTING GUIDE



PANEL CUTOUT (t 0.7~2)




M11X0.75



- NOTES 1 APPLICABLE CRIMP CONTACT:HR12-SC-212(CL112-0408-9)
APPLICABLE WIRE:AWG#26 TO #30(COVERED WIRE MAX. OUTSIDE DIA.Ø1)
APPLICABLE CONTACT REMOVAL TOOL(EXTRACTION TOOL):HR12-SC-TP(CL150-0050-3)
2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. 5 TO BE 2 N·m.
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF. NO. 5 FROM LOOSENING.

3	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0				
2	STAINLESS STEEL			5	BRASS 	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED		4	PHOSPHOR BRONZE	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS

 HIROSE ELECTRIC CO., LTD.	UNITS mm		SCALE 2 : 1		COUNT 2	DESCRIPTION OF REVISIONS DIS-C-003736	DESIGNED HR. SATO	CHECKED HY. KISHI	DATE 14.11.25
	APPROVED :MO. SATOH		07.03.13		DRAWING NO. EDC4-022885-71				
	CHECKED :EJ. KUNII		07.03.12		PART NO. HR10A-10R-10SC(71)				
	DESIGNED :TO. HORII		07.03.09		CODE NO. CL110-0606-0-71				
	DRAWN :MK. SATO		07.03.09		 				