

SHEET 1 OF 1




PANEL CUTOUT
MAX. PANEL THICKNESS 6mm








SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OPEN	1-2



CONTACT CONFIGURATION
FUNCTION: OFF-ON







NOTE:
1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
   X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 20A/250VAC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 100MΩ @ 500VDC
8. DIELECTRIC STRENGTH: 1,500 VAC
9. CONTACT RESISTANCE: 50mΩ
10. OPERATING TEMP.: -40°C to 85°C
11. TRAVEL: 3.5mm
12. ▲ DENOTES CRITICAL PARAMETER.
▲13. LAMP VOLTAGE: 12V
▲14. ILLUMINATION COLOR: GREEN
▲15. INGRESS PROTECTION: IP67
▲16. HARDWARE SUPPLIED: O-RING AND HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY
A	ECO-104170	RELEASE	06/09/26	JS

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E·SWITCH®

OBJECT ID 100132974

TITLE PVHC7F23SS334

SCALE	DATE	DR	DWG	REV
3:2	6/5/2026	JS	52-PVHC7F23SS334	A