

	REVISIONS			
R	EV	DESCRIPTION	DATE	APPV
	Α	INITIAL RELEASE OF LINX INTERNAL DRAWING	01/MAR/19	CLL



## NOTES: (UNLESS OTHERWISE SPECIFIED)

- 1. ALL DIMENSIONS ARE IN MILLIMETERS [IN].
- 2. DIMENSIONS APPLY AFTER FINISHING.
- 3. MANUFACTURE TO BE COMPLIANT WITH EU ROHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
- 4. ELECTRICAL SPECIFICATIONS ARE LISTED FOR REFERENCE ONLY. SEE LINX DATA SHEET FOR **CURRENT PROPERTIES.** 
  - 1. IMPEDANCE:  $50\Omega$
  - 2. FREQUENCY RANGE: 0 TO 6 GHz
- 5. MECHANICAL SPECIFICATIONS:
  - 1. TEMPERATURE RANGE: -55°C TO +155°C
  - RECOMMENDED TORQUE: 0.57 Nm (5 in lbs)
  - CONNECTOR DURABILITY: 500 CYCLES MIN.
  - 4. INTERFACE: SMA TYPE IAW MIL-STD-348B
- 6. PRODUCT QUALIFIED IAW LINX TEST PLAN AT CURRENT REVISION.
- 7. UNLISTED DIMENSIONS ARE CONTROLLED BY SOLID MODEL AT LATEST REVISION.
- 8. LABEL LOT BAG AND BOX IAW LINX LABEL DRAWING [MEC-LBL-4x2.5-PAPER-ID]

WARNING: THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT IS THE SOLE PROPERTY OF LINX TECHNOLOGIES, AND SHALL BE TREATED AS SUCH. NO DISCLOSURE OR REPRODUCTION OF THIS DOCUMENT IS PERMITTED, IN WHOLE OR IN PART, WITHOUT THE EXPRESS WRITTEN PERMISSION OF LINX TECHNOLOGIES OR ITS



**GOLD** 



LINX PART NUMBER

CONSMA010 CONSMA010-G

> 159 ORT LANE **MERLIN, OR 97532**

**FINISH NICKEL** 

**GOLD** 

TITLE:

## CONNECTOR IN-LINE SMA RA **JACK TO PLUG**

SIZE DWG. NO. REV C-CONSMA010-X Α SCALE: 3:1 DO NOT SCALE DRAWING SHEET 1 OF 1



**SCALE 1:1**