








SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ☐ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF INSPECTIONS REQUIRED	31
	LAST NO. USED	25





TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN


TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101



CARRIER STRIP VIEW



12047767 & 12064971
SAME AS OTHER CARRIER STRIP VIEW
EXCEPT AS SHOWN

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEAL WITH MODEL FOR ALL DIMENSIONS NOT SHOWN
FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR
TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA)
2. TERMINAL ENGAGE 3N TO 10N TERMINAL DISENGAGE 1.5N TO
WHEN MATED TO A 0.81 THICK X 1.5 WIDE HARDENED STEEL
3. "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE SERIAL
NUMBER (I01, P02, P03, ETC.)
4. DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR
SPRING OR ANY MOVING PART OF THIS TERMINAL. SEVERE
OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL
5. MATERIAL USED IS C654 - TIN PLATED SILICON BRONZE

DRAWING NUMBER							
12047884							
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P	
A1x3	10:1	2 OF 2	1 OF 7	R	23	-	

			0.25 X .29		13964643	01	AC	RESTRICTED			SEE NOTE #S	1-0.8	.17	2.4-1.7	101	4.2	2.8	10.0B	3	2.6	X
			0.25 X .29		13964351	01	AC	RESTRICTED			SEE NOTE #S	0.5-0.35	.21	2.2-1.3	101	3.5	2.1	10.0B	-	2.1	X
			0.25 X .29		13737252	01	AD	-			METAL COPPER ALLOY TIN PLATED	0.22-0.13	.25	1.1-0.81	104	1.9±0.2	1.6±0.15	10.0B	1.9	1.45	X
			0.25 X .29		13717766	03	AN	-			METAL COPPER ALLOY TIN PLATED	0.21	2.1	1.3-1.2	101	4.2	2.8	10.0B	-	2.1	X
			0.25 X .29		15305306	03	AN	-			METAL COPPER ALLOY TIN PLATED	0.35-0.5	.25D	104	4.2	2.8	10.0B	-	2.1	X	
			0.25 X .29		12160812	03	AN	-			METAL COPPER ALLOY SELECTIVE GOLD PLATED	1-0.8-0.5	.17	2.4-1.7	101	4.2	2.8	10.0B	-	2.1	X
			0.25 X .29		12642420	B1	AL	-			METAL COPPER ALLOY TIN PLATED	0.21	2.1	2.4-1.7	101	4.2	2.8	10.0B	-	2.1	X
			0.25 X .29		12064971	06	AL	-			METAL COPPER ALLOY TIN PLATED	0.5-0.35	.21	2.2-1.3	101	3.5	2.1	10.0B	-	2.1	X
			0.25 X .29		12052466	07	AJ	-			METAL COPPER ALLOY TIN PLATED	0.2	2.4	1.4	104	2.6	1.5 ±0.1	10.0B	-	2.1	X
			0.25 X .30-18		12049460	F2	AL	-			METAL COPPER ALLOY TIN PLATED	16	16	2.6±2.4B	103	4.2	3.6	10.0B	-	2.1	X
			0.25 X .30-18		12047671	11	AN	-			METAL COPPER ALLOY TIN PLATED	1-0.8	.24	2.4-1.7	101	4.2	2.8	10.0B	3	2.6	X
			0.25 X .30-18		12047682	F2	AL	-			METAL COPPER ALLOY TIN PLATED	0.35	.22	2-1.84	101	3.4	2.2	10.0B	-	2.1	X
PART NO	REV	N/P	MAT'L SYM	MAT'L SPEC	PART NO	REV	N/P	RESTRICTED	UNPLATED	PLATED	MAT'L SPEC	SIZE (MM)	CORR	DIA	TYPE	F ±0.3	G ±0.2	R	(U)	(V)	UNSEAL

DIM
REF
LIN
DIMEN
FROM
TO
TOLER