








NOTE:
Technical Requirement:The dimension with" * " is for safety standard.

REV.	DESCRIPTION	DESIGN	APPROVAL	DATE
A	NEW	JING LIU	QS LIU	2017.9.27



X. ± 0.6	X.° $\pm 1^\circ$	DWG TYPE: PRODUCT DRAWING	 TIGER Part number CA-C8-AU			
.X ± 0.4	.X° $\pm 0.6^\circ$					
.XX ± 0.10	.XX° $\pm 0.3^\circ$	MOUID NO: AC-P0037-x	TITLE: SAA Two PIN PLUG			
UNITS	mm					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF LUXSHARE-ICT AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF LUXSHARE-ICT		APPD: 欧阳光仁	DWG NO: A12-0037-AC2-1			
		CHKD: 刘秋顺				
		DRAW: 刘景		SCALE	SHEET	REV.
				NONE	1/1	A

1	H03VVH2-F 2x0.75 OD:3.45*5.6	Flat Cable
NO.	SPECIFICATION	Remark

Technical Requirement:The dimension with" * " is for safety standard.




X. ± 0.6	X.° $\pm 1^\circ$	DWG TYPE: PRODUCT DRAWING	TIGER Power Supplies Part number CA-C8-AU			
.X ± 0.4	.X° $\pm 0.6^\circ$					
.XX ± 0.10	.XX° $\pm 0.3^\circ$	MOUID NO: AC-C0102-x	TITLE: VDE C7 CONNECTOR			
UNITS	mm					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF LUXSHARE-ICT AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF LUXSHARE-ICT		APPD: 欧阳光仁	DWG NO: A12-0102-AC2-4			
		CHKD: 刘秋顺				
		DRAW: 刘景		SCALE NONE	SHEET 1/1	REV. A

	SCALE	SHEET	REV.
	NONE	1/1	A

8		7		6		5		4		3		2		1			
E	Item			Specification						REV.		DESCRIPTION		DATE			
	Construction item			ComponentA						A		NEW		2013.07.25			
	Conductor	Cross section		0.75mm ²													
		Material		Bare Copper													
		Size		38/0.16±0.008mm													
D	Insulation	Material		PVC													
		Thickness		0.5mm Ref													
		O.D.		2.2±0.08 mm													
		Insulation NO.		2(Brn,Blue)													
	Layer	Direction		--													
		Diameter		--													
	Jacket	Material		PVC													
		Diameter		3.45*5.6±0.15 mm													
		Color		Black													
		Extrusion		Solid													
		Surface		Plane													
C	Marking	Marking color		White													
		Marking Content		LIGHT DUTY FLAT 4V-75/V-75 250/250V SAA091180EA <VDE> ◀SABS▶▲Ⓢ CABO IEC 60227-5 H03VVH2-F 300/300V 2x0.75mm ² ASAP TECHNOLOGY(JiangXi) CCC A062059 60227 IEC 52(RVV) 300/300V 2x0.75mm ² ASAP TECHNOLOGY(JIANGXI) CO.,LIMITED													
Electric Characters																	
1.Voltage rating :300/300V				2.2 The cable : 2KV AC/5min at 20±5℃ in the water													
2.Dielectric strength : AC-500V/0.15 sec MIN				3.Insulation resistance : 0.010MΩ/km at 70℃ min.													
2.1 Insulation: 1.5KV AC/5min at 20±5℃ in the water				4.Conductor resistance: 26Ω/km at 20℃ max.													
Physical Characters:																	
1.Flame test of cable: no spreading combustion test				3.Tensil strength test are before aging :													
1.1 The interval Which the scorch part and the bottom of top clamp : ≧50mm				3.1 Insulation: ≧10N/mm ²													
				3.2 Sheath : ≧10N/mm ²													
2.Structure inspection:				4.Tensil strength test are after aging:													
2.1 Insulation: 0.5mm min. average thickness ,				4.1 Insulation: The changes of the before and after aging is ±20%													
0.35mm min. at any point				4.2 Sheath: The changes of the before and after aging is ±20%													
2.2 Sheath : 0.6mm min. average thickness,				5.Elongation before aging:													
0.44mm min. at any point				5.1 Insulation: ≧150%													
				5.2 Sheath : ≧150%													
				6. Elongation after aging:													
				6.1 Insulation: The changes of the before and after aging is ±20%													
8		7		6		5		4		3		2		1			

6.2 Sheath: The changes of the before and after aging is ±20%		9.Low temperature bend test;	
7. Weightlessness test:		9.1 Insulation: No any chasm	
7.1 Insulation: ≡2.0mg/cm ²		9.2 Sheath: No any chasm	
7.2 Sheath: ≡2.0mg/cm ²		10.Low temperature attack test of the cable:	
8. High temperature pressure test:		10.1 No any chasm at -15℃ 16H LOAD 200g.	
8.1 Insulation: impress depth≡		11.Thermal shock test :	
50% average thickness of Insulation		11.1 Insulation: No any chasm	
8.2 Sheath: impress depth≡		11.2 Sheath: No any chasm	
50% average thickness of Sheath		12.Circumnutate test of The cable:	
		12.1 No turnoff and short circuit	
Harmful material and process control, please follow DOC NO "QW-Q-043"			



Conductor

Insulation

Jacket

34.64±4%	
單重(G/M)	

X.± *	X.°±	UNITS	NAME(INTENDED USE)	 TIGER Power Supplies	Part number CA-C8-AU	
						SAA H03VVH2-F/RVV(52) 2*0.75MM
.X± *	.X°±	mm				
.XX± *	.XX°±					
.XXX± *	.XXX°±	MATL			TITLE: SAA H03VVH2-F/RVV(52) 2*0.75MM ² 3.45*5.6±0.15 mm Black	
		FINISH	APPD: 杨保根	DWG NO: 00A-222100-001R		
			CHKD: 欧阳光仁			
		Q'TY	DR: 刘波	 		
				SCALE	SHEET	REV.
				NONE	1/1	A