



CLIFF


ISS.	AMEND	DATE
1	ISSUED	01/03/21
2	UPDATE MATERIALS	25/03/22














VARIANTS	
PART NO.	**HOLE DETAILS**
CP30620SM	HOLE Ø3.2 x CSK 90° x Ø5.85
CP30620SMX1	PLAIN HOLE Ø3.2

Material:
1. RJ45 In-Line Coupler: ABS UL94-V0 Fully Shielded
2. RJ45 In-Line Coupler Contact: Phosphor Bronze, 3-50 micro inches gold plating over nickel plate.
3. PCB: FR4
4. FT Frame: Zinc Diecast, Nickel Plated

Performance:
1. T568A & T568B wiring.
2. Meet ISO/IEC 11801 and EN50173
3. Meet ANSI/TIA/EIA 568B.2
4. Rating: 125VAC RMS 1.5A
5. Operating Temperatures: Min -10°C Max +70°C

RoHS ✓ **COMPLIANT**

TOLERANCE
NO DEC. PLACE ±
1 DEC. PLACE ±
2 DEC. PLACE ±
HOLE Ø ±
ANGLES ±
UNLESS OTHERWISE STATED

Cliff Electronic Components Ltd.
76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2021

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK. | 3rd ANGLE PROJECTION: | DO NOT SCALE

MATERIAL: See Notes
FINISH: See Notes
DRAWN: T.J.O. | APPROVED: D.P.J.

TITLE: FRONT MOUNT METAL SLIM FT FTP CAT5e RJ45 SHIELDED

DRWG. No. CP30620SM | FORM: A4DRWGH