





REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	FEB.02,2012	L.CHAN



RECOMMENDED PANEL CUTOUT



LOCATE HOLES

$\phi \phi.005[0.13]$

POSITION DIMENSIONS
ARE BASIC

RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

MATERIALS:

HOUSING : HIGH TEMP. ENGINEERING THERMOPLASTIC,
BLACK, FLAMMABILITY RATING UL94V-0

CONTACTS: PHOSPHOR BRONZE

PLATING: REFER PART NUMBER FOR GOLD THICKNESS
ON MATING SURFACE

50 μ " [1.27 MICRONS]

MIN. NICKEL UNDERPLATE

100 μ " [2.54 MICRONS]

MIN. MATTE TIN ON CONTACT TAILS.

SHIELD: COPPER ALLOY

PLATING: NICKEL

AMPHENOL PART NUMBER: RJE15-188-5X10

GOLD PLATING

1 = 6 μ "

2 = 15 μ "

3 = 30 μ "

4 = 50 μ "

DRAWN <i>G.HSIA</i>		DATE <i>FEB.02,2012</i>	Amphenol Canada Corp.			
DESIGNED						
CHECKED <i>L.CHAN</i>		<i>FEB.02,2012</i>	TITLE 1 PORT SMT MODULAR JACK, 8 POSITION, 8 CONTACT, SHIELD WITH DIP TAIL SIDE & TOP TABS – RoHS COMPLIANT			
I. E. APPRD.						
Q. A. APPRD.			DWG. DRAWING NO. P–RJE15–188–5X10			
DWG. APPRD.						
ENG. REL. NO.			DWG.	DRAWING NO.		REV. A
REF.						
DIMENSIONS ARE IN <i>mm</i>		CODE ID. NO. <i>03554</i>	SCALE	WT. _____	SURF. _____	SHEET <i>1</i> OF <i>1</i>

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.