



NOTE:
ONLY SUITABLE FOR RT360 SERIES 1403 AND 1604
LAYOUT WITH "EC" PART NUMBER CONNECTOR



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASED DRAWING	Feb-15-2023	Joe	TOMMY
A2	-	Add deminsion A and B	Mar-15-2023	Joe	TOMMY
A3	-	UPDATED THE NOTE	Mar-20-2025	Joe	TOMMY

P/N	WIRE RANGE	CONTACT PLATING(MATING AREA)	A	B
MS10A23S-25W	1.5~2.5mm ²	SILVER PLATING OVER NICKEL.	3.5mm	2.3mm
MS10A23F-25W	1.5~2.5mm ²	GOLD FLASH PLATING OVER NICKEL.	3.5mm	2.3mm
MS10A23S-63W	4~6mm ²	SILVER PLATING OVER NICKEL.	4.7mm	3.75mm
MS10A23F-63W	4~6mm ²	GOLD FLASH PLATING OVER NICKEL.	4.7mm	3.75mm

- NOTES: (UNLESS OTHERWISE SPECIFIED)
- MATERIAL:
 - CONTACT BODY: COPPER ALLOY.
 - POSITIONING CLIP: COPPER ALLOY.
 - SPECIFICATIONS:
 - CURRENT RATING: 45A(MAX).
 - TERMINATION TYPE: CRIMPING.
 - WIRE RANGE: SEE TABLE
 - SUITABLE CONTACT: MP10A23*&MP10A23*L&MP10A23*-25 & MP10A23*-63.
 - RoHS COMPLIANT.
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference =		SIGNATURES DRAWN: Joe CHECKED: Orion ENGINEER: APPROVAL: Tommy CUSTOMER:	DATE Mar-20-25 Mar-21-25 Mar-25-25
MATERIAL SPECIFICATIONS:		EcoMate RM, SOCKET CONTACT MACHINE, 8# (Ø3.6mm)	
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
NEXT ASSY:		SIZE B	TYPE C
		SCALE NONE	DWG NO: MS10A23*-25W/63W
		REVISION A3	SHEET 1 OF 1

TITLE: EcoMate RM, SOCKET CONTACT, MACHINE, 8# (Ø3.6mm)
DWG NO: MS10A23*-25W/63W
REV: A3
SH: 1
OF: 1