

EVN2000 Series Limit Switch



Features

- Innovative wiring system
- Integrated cable gland
- EN 50047
- Designed to meet switch requirement within EN 81-1
- Snap action basic switch with 4 mm air gap
- IP 66/67 Enclosure rating, EN 60529. NEMA 1, 12, 13
- Positive opening operation of Normally Closed contacts conforming to IEC/EN 60947-5-1 annex K
- Double insulated switch element
- Extremely compact plastic housing
- High switching current capability

Description

The EVN2000 series limit switch is an innovative product which has been developed to address a need highlighted by Original Equipment Manufacturers (OEM), "Ease of Wiring". The new design eliminates the need to gain access to the inside of the housing, which in turn makes a housing cover, cover screws and gasket obsolete.

WARNING

MISUSE OF DOCUMENTATION

- The information presented in this product sheet (or catalogue) is for reference only. **DO NOT USE** this document as product installation information.
- Complete installation, operation and maintenance information is provided in the instructions supplied with each product.

Failure to comply with these instructions could result in death or serious injury.

Benefits

- Reduced wiring time, up to 50 % savings can be achieved
- Provides a truly global product by removing the need for conduit or cable gland hardware
- Interchangeable with most major competitors
- Meets switch requirements within "Safety rules for the construction and installation of lifts - electric lifts"
- 1 Normally Closed, 1 Normally Open circuit conforming to EN 81-1
- Suitable for wet applications
- Guaranteed opening of the normally closed circuit in the event of contacts welding
- No earth connection required, internal or external
- Suitable where space is at a premium

Typical applications

- Material handling
- Elevators and moving stairs
- Scissor/platform lifts
- Food and beverage
- Manufacturing

WARNING

PERSONAL INJURY

DO NOT USE these products as safety or emergency stop devices, or in any other application where failure of the product could result in personal injury.

Failure to comply with these instructions could result in death or serious injury.

EVN2000 Series Limit Switch

Technical information

Specifications

Mechanical life:	up to 10 million operations
Degree of protection:	IP 66/67, EN 60529 NEMA/UL type 1, 12, 13
Operating temperature:	-25 °C to 85 °C (-13 °F to 185 °F)
Storage temperature:	-40 °C to 85 °C (-40 °F to 185 °F)
Standards/approvals:	IEC/EN 60947-5-1 EN 50047 UL 508 UL 746C EN 60529 EN 81-1
Electrical rating:	AC15, A300 DC13, Q300
Rated insulation voltage:	320 V
Rated impulse withstand:	2500 V
Thermal current:	10 A
Short circuit withstand:	SCPD 10 A quick acting fuse (IEC 269.1 gG-type)
Contact material:	Silver
Circuit type:	1NC/1NO Single pole, single throw, double break Contact type Zb
Cable/enclosure:	0,75 mm ² to 1,5 mm ² (16-18 AWG)
Shock:	IEC 68-2-27 (BS 2011, Part 2.1 Ea)
Vibration:	IEC 68-2-6 (BS 2011, Part 2.1 Fc)
Bump:	IEC 68-2-29 (BS 2011, Part 2 LeB)
Damp heat steady state:	IEC 68-2-3 (BS 2011, Part 2.1 Ca)


Order guide

Description	Catalogue Listing
Side Rotary Lever	EVN2000A
Top Pin Plunger	EVN2000B
Top Roller Plunger, Parallel	EVN2000C
Top Roller Plunger, Perpendicular	EVN2000D


EVN2000 Series Limit Switch

Mounting drawings in mm and (inches)


EVN2000A





EVN2000C



EVN2000B



EVN2000D



Harax® is a registered trademark of HARTING KGaA

Warranty/Remedy

Honeywell warrants goods of its manufacture as being free of defective material and faulty workmanship. Contact your local sales office for warranty information. If warranted goods are returned to Honeywell during that period of coverage, Honeywell will repair or replace without charge those items it finds defective. The foregoing is Buyer's sole remedy and **is in lieu of all other warranties, expressed or implied, including those of merchantability and fitness for a particular purpose.**

While we provide application assistance, personally, through our literature and the Honeywell web site, it is up to the customer to determine the suitability of the product in the application.

Specifications may change at any time without notice. The information we supply is believed to be accurate and reliable as of this printing. However, we assume no responsibility for its use.

Sales and Service

Honeywell serves its customers through a worldwide network of sales offices and distributors. For application assistance, current specifications, pricing or name of the nearest Authorised Distributor, contact your local sales office or: INTERNET: www.honeywell.com/sensing
E-mail: info.sc@honeywell.com

ASIA PACIFIC

**Sensing & Control
Asia Pacific Headquarters**
Phone: +(65) 355-2828
Fax: +(65) 445-3033

Australia
Honeywell Limited
Phone: +(61) 2-9370-4500
FAX: +(61) 2-9370-4525
Toll Free 1300-36-39-36
Toll Free Fax: 1300-36-04-70

China – PRC - Beijing
Honeywell China Inc.
Phone: +(86-10) 6561-0208
Ext. 205
Fax: +(86-10) 6561-0618

China – PRC - Shanghai
Honeywell China Inc.
Phone: (86-21) 6354-9181
Fax: (86-21) 6354-2248

China - Hong Kong S.A.R.
Honeywell Ltd.
Phone: +(852) 2331-9133
Fax: +(852) 2331-9998

China – PRC - Chengdu
Honeywell China Inc.
Phone: +(86-28) 6786-348
Fax: +(86-28) 6787-061

China – PRC - Guangzhou
Honeywell China Inc.
Phone: +(86-20) 3879-1169
Fax: +(86-20) 3879-1269

China – PRC - Shenzhen
Honeywell China Inc.
Phone: +(86) 755-518-1226
Fax: +(86) 755-518-1221

Indonesia
Honeywell Indonesia Pte Ltd.
Phone: +(6221) 521-3330
FAX: +(6221) 521-3735

India
TATA Honeywell Ltd.
Phone: +(91) 20 6875-532 /
6875 534
Fax: +(91) 20 6875-992

Japan
Honeywell Inc
Phone: +(81) 3 5440 1395
Fax: +(81) 3 5440 1314

South Korea
Honeywell Korea Co Ltd
Phone: +(822) 799-6114
Fax: +(822) 792-9011

Malaysia
Honeywell Engineering Sdn
Bhd
Phone: +(60-3) 7958-4988
Fax: +(60-3) 7958-8922

New Zealand
Honeywell Limited
Phone: +(64-9) 623-5050
Fax: +(64-9) 623-5060
Toll Free (0800) 202-088

Philippines
Honeywell Systems
(Philippines) Inc.
Phone: +(63-2) 636-1649
Fax: +(63-2) 636-1650

Singapore
Honeywell South East Asia
Phone: +(65) 355-2828
Fax: +(65) 445-3033

Thailand
Honeywell Systems (Thailand)
Ltd.
Phone: +(662) 693-3099
FAX: +(662) 693-3085

Taiwan R.O.C.
Honeywell Taiwan Ltd.
Phone: +(886-2) 2245-1000
FAX: +(886-2) 2245-3242

EUROPE

Austria
Honeywell Austria GmbH
Phone: +(43) 1 727 80 366/246
FAX: +(43) 1 727 80 337

Belgium
Honeywell SA/NV
Phone: +(32) 2 728 2522
FAX: +(32) 2 728 2502

Bulgaria
Honeywell EOOD
Phone: +(359) 2 79 40 27
FAX: +(359) 2 79 40 90

Czech Republic
Honeywell spol. s.r.o.
Phone: +(420) 2 6112 3469/
3424
FAX: +(420) 2 6112 3461

Denmark
Honeywell A/S
Phone: +(45) 39 55 55 55
FAX: +(45) 39 55 55 58

Finland
Honeywell OY
Phone: +(358) 9 3480101
FAX: +(358) 9 34801375

France
Honeywell SA
Phone: +(33) 1 60 19 80 40
FAX: +(33) 1 60 19 81 73

Germany
Honeywell AG
Phone: +(49) 69 8064 444
FAX: +(49) 69 8064 442

Hungary
Honeywell Kft.
Phone: +(36 1) 451 4300
FAX: +(36 1) 451 4343

Italy
Honeywell S.p.A.
Phone: +(39) 02 92146 450/456
FAX: +(39) 02 92146 490

The Netherlands
Honeywell B.V.
Phone: +(31) 20 565 69 11
FAX: +(31) 20 565 66 00

Norway
Honeywell A/S
Phone: +(47) 66 76 20 00
FAX: +(47) 66 76 20 90

Poland
Honeywell Sp. zo.o
Phone: +(48) 22 606 0900
FAX: +(48) 22 606 0901

Portugal
Honeywell Portugal Lda
Phone: +(351 21) 424 50 00
FAX: +(351 21) 424 50 99

Romania
Honeywell Bucharest
Phone: +(40) 1 2110076
FAX: +(40) 1 2103375

**Commonwealth of
Independent States (CIS)**
Z.A.O. Honeywell
Phone: +(7 095) 796 98 36
FAX: +(7 095) 796 98 93

Slovak Republic
Honeywell s.r.o.
Phone: +(421 7) 58247 403/400
FAX: +(421 7) 58247 415

South Africa (Republic of)
Honeywell Southern Africa
Honeywell S.A. Pty. Ltd
Phone: +(27) 11 805 1211
FAX: +(27) 11 805 1354

Spain
Honeywell S.A.
Phone: +(34) 91 313 6100
FAX: +(34) 91 313 6129

Sweden
Honeywell AB
Phone: +(46) 8 775 55 00
FAX: +(46) 8 775 56 00

Switzerland
Honeywell AG
Phone: +(41) 1 855 24 40
FAX: +(41) 1 855 24 45

Turkey
Honeywell Turkey A.S.
Phone: +(90) 216 464 4764
FAX: +(90) 216 464 4794

United Kingdom
Honeywell Control Systems Ltd
Phone: +(44) 1698 481481
FAX: +(44) 1698 481276

**Mediterranean & African
Distributors**
Honeywell SpA
Phone: +(39) 2 921 46 232
FAX: +(39) 2 921 46 233

Middle East Headquarters
Honeywell Middle East Ltd.
Phone: +(9712) 443 2119
FAX: +(9712) 443 2536

NORTH AMERICA

Canada
Honeywell LTD
Phone: 1-800-737-3360
FAX: 1-800-565-4130

USA
Honeywell
Sensing and Control,
International Headquarters
Phone: 1-800-537-6945
1-815-235-6847
FAX: 1-815-235-6545
E-mail:
info.sc@honeywell.com

LATIN AMERICA

Argentina
Honeywell S.A.I.C.
Phone: +(54-11) 4383-3637
FAX: +(54-11) 4325-6470

Brazil
Honeywell do Brasil & Cia
Phone: +(55-11) 7266-1900
FAX: +(55-11) 7266-1905

Chile
Honeywell Chile, S.A.
Phone: +(56-2) 231-6688
FAX: +(56-2) 231-6679

Columbia
Honeywell Columbia, S.A.
Phone: +(57-1) 623-3239/
3051
FAX: +(57-1) 623-3395

Ecuador
Honeywell S.A.
Phone: +(593-2) 981-560/1
FAX: +(593-2) 981-562

Mexico
Honeywell S.A. de C.V.
Phone: +(52) 55 5259-1966
FAX: +(52) 55 5570-2985

Puerto Rico
Honeywell Inc.
Phone: +(809) 792-7075
FAX: +(809) 792-0053

Venezuela
Honeywell CA
Phone: +(58-2) 238-0211
FAX: +(58-2) 238-3391

This publication does not constitute a contract between Honeywell and its customers. The contents may be changed at any time without notice. It is the customer's responsibility to ensure safe installation and operation of the products. Detailed mounting drawings of all products illustrated are available on request.
© Honeywell 2001. All rights reserved.

Honeywell

Sensing and Control

www.honeywell.com/sensing

Honeywell Control Systems Ltd
Newhouse Industrial Estate
Motherwell, Lanarkshire ML1 5SB
Scotland, UK