

ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM
A	503988000	2.5 W-W CRIMP PIN (CHAIN)	1	PC
B	--	LEAD FREE SOLDER BAR SAC 305	A/R	KG

FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A	--	28 AWG	UL 1007	BLACK




TABLE		
FG PART #	L	TITLE
2291151142	150±5	CP3.3 28AWG M-S 150 mm
2291151144	300±5	CP3.3 28AWG M-S 300 mm

NOTE:
 1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
 2. THE PRODUCT SPECIFICATION RELIES ON THE TERMINALS & WIRE SPEC.
 3. FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. TINNING DIA MUST BE 0.7MM MAX.

A	INITIAL RELEASE	ER	17-MAR-2025	NA	NA
REVISION	CHANGE NOTE	EC NO	DATE	CUSTOMER P/N	CUSTOMER REV

REVISION HISTORY					
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
CURRENT REV DESC:					
EC NO: 816292			2025/03/17		
DRWN: BHARAB5			2025/03/19		
CHK'D: NAVEEB6			2025/03/20		
APPR: RPAI01			2025/03/20		
INITIAL REVISION:			DOCUMENT NUMBER		
DRWN: BHARAB5			2291151142		
APPR: RPAI01			PSD 000 A		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER
			A3-SIZE	229115	SEE TABLE
			GENERAL MARKET		SHEET NUMBER
					1 OF 1

DETAIL	DESCRIPTION	DETAIL	DESCRIPTION
	Continues Taping		PVC sleeve or Silicon sleeve
	HST		T Dimension
	Woven Braid		Convulated Tube
	Spot Taping		Customer Specific requirements

DOCUMENT STATUS	P1	RELEASE DATE	2025/03/20	05:22:42
-----------------	----	--------------	------------	----------