

ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM
A	503978000	2.5/3.3 CONN CRIMP RECEPT (CHAIN)	1	PC
B	--	LEAD FREE SOLDER BAR SAC 305	A/R	KG

FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A	--	28 AWG	UL 1007	BLACK




TABLE		
FG PART #	L	TITLE
2291191122	150±5	CP3.3 28AWG F-S 150 mm
2291191124	300±5	CP3.3 28AWG F-S 300 mm

- NOTE:
1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
 2. THE PRODUCT SPECIFICATION RELIES ON THE TERMINALS & WIRE SPEC.
 3. FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. TINNING DIA MUST BE 0.7MM MAX.

A	INITIAL RELEASE	ER	17-MAR-2025	NA	NA
REVISION	CHANGE NOTE	EC NO	DATE	CUSTOMER P/N	CUSTOMER REV

REVISION HISTORY

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

CURRENT REV DESC:

EC NO: 816292

DRWN: BHARAB5 2025/03/17

CHK'D: NAVEEB6 2025/03/19

APPR: RPAI01 2025/03/20

INITIAL REVISION:

DRWN: BHARAB5 2025/03/17

APPR: RPAI01 2025/03/20

molex

SEE TABLE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER: 2291191122

DOC TYPE: PSD

DOC PART: 000

REVISION: A

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING: A3-SIZE

SERIES: 229119

MATERIAL NUMBER: SEE TABLE

CUSTOMER: GENERAL MARKET

SHEET NUMBER: 1 OF 1

DETAIL	DESCRIPTION	DETAIL	DESCRIPTION
	Continues Taping		PVC sleeve or Silicon sleeve
	HST		T Dimension
	Woven Braid		Convulated Tube
	Spot Taping		Customer Specific requirements

DOCUMENT STATUS	P1	RELEASE DATE	2025/03/20	05:22:43
-----------------	----	--------------	------------	----------