




7.5 mm Pitch **Standard Profile** Rising Clamp Terminal

Features

- 2 & 3 pole double interlocking mechanism for increased strength
- 4-12 pole pre-assembled
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 2.5mm² cable entry
-  approved
- cUL applied for
- Guided pin alignment



CTB0110 Series



CTB0110 Series [click to enlarge](#)

Type No.	Poles	Length
CTB0110/2	2	15mm
CTB0110/3	3	22.5mm
CTB0110/4	4	30mm
CTB0110/5	5	37.5mm
CTB0110/6	6	45mm
CTB0110/7	7	52.5mm
CTB0110/8	8	60mm
CTB0110/9	9	67.5mm
CTB0110/10	10	75mm
CTB0110/11	11	82.5mm
CTB0110/12	12	90mm


Specification

Rating	20A/750V
Dielectric strength	•3kV/60sec
Insulation resistance	•5M•
Working temperature	-20•C to 125•C
Short period	160°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	5μ tinned, nickel plated brass
Wire clamp	Nickel plated brass
Screw/torque	M3 steel, 6μ zinc colour passivated and tropicalised/0.5Nm
Recommended PCB hole size	ø1.3mm


7.5 mm Pitch **Standard Profile 90°** Rising Clamp Terminal

Features

- 2 & 3 pole double interlocking mechanism for increased strength
- 4-12 pole pre-assembled
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 2.5mm² cable entry



CTB0115 Series





CTB0115 Series [click to enlarge](#)

For other dimensions see CTB0110

Type No.	Poles	Length
CTB0115/2	2	15mm
CTB0115/3	3	22.5mm
CTB0115/4	4	30mm
CTB0115/5	5	37.5mm
CTB0115/6	6	45mm
CTB0115/7	7	52.5mm
CTB0115/8	8	60mm
CTB0115/9	9	67.5mm
CTB0115/10	10	75mm
CTB0115/11	11	82.5mm

Specification

Rating	20A/750V
Dielectric strength	•3kV/60sec
Insulation resistance	•5M•
Working temperature	-20•C to 125•C
Short period	160°C
Moulding	UL94-V0 flame retardant PA66

<ul style="list-style-type: none"> ●  , CE &  approved ● cUL applied for ● Guided pin alignment 	<table border="1"> <tr> <td>CTB0115/12</td> <td>12</td> <td>90mm</td> </tr> </table>		CTB0115/12	12	90mm	retardant PAbb
	CTB0115/12	12	90mm			
			Pin/terminal	5μ tinned, nickel plated brass		
			Wire clamp	Nickel plated brass		
		Screw/torque	M3 steel, 6μ zinc colour passivated and tropicalised/0.5Nm			
		Recommended PCB hole size	ø1.3mm			

- www.camden-electronics.co.uk -