

4

3

2

1

© 2019 TE Connectivity. All Rights Reserved.

THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

DIE ZEICHNUNG ZEIGT DEN 2-DIMENSIONALEN IDEALZUSTAND DES ZUSAMMENBAUTEILS BEZUEGLICH DER KOMPONENTEN ZUR IDENTIFIKATION UND SPEZIFIKATION DER NOTWENDIGEN DIMENSIONEN. HINSICHTLICH DER ORIENTIERUNG UND DER LAGE DER KOMPONENTEN (z.B. BIEGESCHLAFTES KABEL) KOENNEN DIE DELIEFERTEN TEILE VON DER ZEICHNUNG ABWEICHEN, SOFERN DIE FUNKTIONALITAET NICHT BEEINTRAECHTIGT IST.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	NOTE 5 UPDATED	12FEB2020	MZ	PR
	A3	NEW LENGTHS ADDED (-9, 1- -X)	21SEP2020	MZ	TD
	A4	ADD NOTE 6	24 JAN2023	MZ	TD
	A5	PLANT LOCATION CHANGED	27DEC2024	HL	LS

LENGTH SCHEDULE:

TE PART NO.	REV.	LENGTH L [mm]	TOL.	WEIGHT [g]
2362765-1	A	600	+20	9
2362765-2	A	1500	+20	20
2362765-3	A	2000	+25	26
2362765-4	A	2500	+30	32
2362765-5	A	3000	+40	38
2362765-6	A	4000	+40	50
2362765-7	A	7500	+40	92
2362765-8	A	15000	+40	182
2362765-9	A	300	+20	5
1-2362765-0	A	800	+20	11
1-2362765-1	A	900	+20	13
1-2362765-2	A	1000	+20	14
1-2362765-3	A	5000	+40	62
1-2362765-4	A	6000	+40	74
1-2362765-5	A	7000	+40	86
1-2362765-6	A	8000	+40	98
1-2362765-7	A	10000	+40	122

VIEW A

CONNECTOR A

CONNECTOR B

VIEW B

A5

5

TABLE A: PLANT LOCATION CODE

CODE	PLANT LOCATION
MA	MOROCCO
CZ	CZECH REPUBLIC

WIRING SCHEDULE:

CAVITY-NO. CONNECTOR A	WIRE COLOUR	CAVITY-NO. CONNECTOR B
1	WHITE	1
2	GREEN	2

NOTES:

1 PACKAGING:
ASSEMBLY IN TE STANDARD CARTON

2 ELECTRICAL TEST: 100% FOR CONTINUITY AND SHORT CIRCUIT.
ACC. TE SPECIFICATION 108-18857.

3 DIMENSION OF LENGTH IS FOR STRAIGHT CABLE.

4 PRODUCT SPECIFICATION: 108-94568

A5

5

JACKET PRINT:
TE-XX,(THE X IS CODE OF THE MANUFACTURING PLANT LOCATION TO BE CHOSEN FROM THE TABLE A).
100 Mbps MATENet UTP, TE-XX, TE PN, REV., DATE CODE
(DCWYY= D: DAY OF WEEK; CW: CALENDAR WEEK; YY: LAST TWO DIGITS OF YEAR)
THE PRINT MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION.

6 RELEASED CABLE TYPES ACCORDING TE SPECIFICATION 114-94431.

1-2302450-1

2

MATENET, FEMALE INSERT MODUL, BLACK

4

1-1703930-1

4

NANOMQS, RECEPTACLE TERMINAL

3

2302452-1

2

MATENET, FIXATION ELEMENT

2

-

see table

2 POS, CABLE, 0.13 SQMM, UNSHIELDED, ETHERNET

1

TE PART NO.

QTY
- X

DESCRIPTION

ITEM NO.

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.
BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

-

MATERIAL -

-

DWN M. Zelch 26SEP2019

CHK P. Riedel 26SEP2019

APVD T. Dirion 27SEP2019

PRODUCT SPEC see note 4

APPLICATION SPEC -

WEIGHT see table

CUSTOMER DRAWING

TE Connectivity

NAME MATENET, CABLE ASSY, 100 MBPS UTP

-

-

SIZE A2

CAGE CODE 00779

DRAWING NO C=2362765

RESTRICTED TO -

SCALE 2:1

SHEET 1 OF 1

REV A5

1471-9 (3/13)