












THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		
(C) COPYRIGHT		ALL RIGHTS RESERVED.		
CODINGS ACC. TO INTERFACE DRAWING 208-18006				
CODE A	CODE B	CODE C	CODE J	CODE Z
				

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	23JUL2021	HL.F	I.Y
	A3	ECN-21-114446	23AUG2021	HL.F	I.Y



1. CAVITY FOR MATEnet 2Pos. NanoMQS
MALE INSERT MODULE TE PN 2302451-1
 2. CONDITION OF DELIVERY: RETAINER IN OPEN POSITION, IF IN
END LOCKING POSITION AFTER TRANSPORTATION, PLEASE RELOCK
 3. CONTACT SPRINGS FOR ELECTRICAL CONNECTION OF
WIRE SHIELDING
 4. MATERIAL MARKING
 5. AREA FOR CABLE TIE UP TO 2.5mm WIDTH
 6. ASSEMBLY-PN, SEE TABLE
 7. TE INTERFACE DRAWING 208-18006
8. DELIVERY: LOOSE PIECES IN BAG IN BOX
9. 2394145-1 CODE A AS SHOWN
10. CLIP SLOT FEATURES ACCORDING TO EWCAP-005-7, REV D

2394145-9	A	Z	1	MATenet Inline Coupler Sheet	BRASS	SN	5.03	2
			1	MATenet Inline Coupler HSG., Code Z	PBT/PC-GF10	WATER BLUE		1
2394145-7	A	J	1	MATenet Inline Coupler Sheet	BRASS	SN	5.03	2
			1	MATenet Inline Coupler HSG., Code J	PBT/PC-GF10	BEIGE		1
2394145-3	A	C	1	MATenet Inline Coupler Sheet	BRASS	SN	5.03	2
			1	MATenet Inline Coupler HSG., Code C	PBT/PC-GF10	BLUE		1
2394145-2	A	B	1	MATenet Inline Coupler Sheet	BRASS	SN	5.03	2
			1	MATenet Inline Coupler HSG., Code B	PBT/PC-GF10	WHITE		1
2394145-1	A	A	1	MATenet Inline Coupler Sheet	BRASS	SN	5.03	2
			1	MATenet Inline Coupler HSG., Code A	PBT/PC-GF10	BLACK		1
ASSY PN	REV.	CODE	QTY.	DESCRIPTION	MATERIAL	COLOR/ SURFACE	WEIGHT [g]	POS

THIS DRAWING IS A CONTROLLED DOCUMENT.		HWL.FU 23AUG2021 CHK 23AUG2021 F.PAN APVD L.YIN 23AUG2021		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Matenet inline 1p with clip			
		0 PLC ± 0.3 1 PLC ± 0.3 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES ± 0.1		PRODUCT SPEC 108-94568		-	
MATERIAL see table		FINISH see table		APPLICATION SPEC 114-94431		SIZE A2	CAGE CODE -
DWG NO. 7052 - TOLERANCES AND ACCEPTANCE CONDITIONS DIN 9072 - Toleranzen und Abnahmegestaltungen		WEIGHT see table		DRAWING NO C=2394145		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 2:1		SHEET 1 of 1	
				REV A3			