

ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM
A	2147205010	Zero-Hachi 0.8 CRIMP TERM #28-30 AU PLT	1	PC
B	--	SOLDER BAR	A/R	KG

FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A	--	28 AWG	UL 10064	BLACK




TABLE		
FG PART #	L	TITLE
2290972222	150±5	Zero Hachi 0.8 F-S 28 AWG Au 150 mm
2290972224	300±5	Zero Hachi 0.8 F-S 28 AWG Au 300 mm

- NOTE:
1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
 2. THE PRODUCT SPECIFICATION RELIES ON THE TERMINALS & WIRE SPEC.
 3. FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. TINNING DIA MUST BE 0.6MM MAX.

A	INITIAL RELEASE	ER	09-APR-2025	NA	NA
REVISION	CHANGE NOTE	EC NO	DATE	CUSTOMER P/N	CUSTOMER REV

REVISION HISTORY

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

CURRENT REV DESC:

EC NO: 818425

DRWN: BHARAB5 2025/04/08

CHK'D: NAVEEB6 2025/04/09

APPR: RPAI01 2025/04/09

INITIAL REVISION:

DRWN: BHARAB5 2025/04/08

APPR: RPAI01 2025/04/09

molex

SEE TABLE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER: **2290972222**

DOC TYPE: PSD DOC PART: 000 REVISION: A

MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET SHEET NUMBER: 1 OF 1

DETAIL	DESCRIPTION	DETAIL	DESCRIPTION
	Continues Taping		PVC sleeve or Silicon sleeve
	HST		T Dimension
	Woven Braid		Convuluted Tube
	Spot Taping		Customer Specific requirements

FUNCTIONAL SYMBOLS	DIMENSION UNITS	SCALE
	mm	NTS
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	ANGULAR TOL ± °	
	4 PLACES ±	
	3 PLACES ±	
	2 PLACES ±	
	1 PLACE ±	
	0 PLACES ±	
DIVISIONAL SYMBOLS	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	