

ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM
A	5055721100	2.0W/B REC CRIMP TERM CHAIN H>F G010	1	PC
B	-	LEAD FREE SOLDER BAR	AR	KG

FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A	-	22 AWG	UL 1061	BLACK




TABLE		
FG PART #	L	TITLE
2298101222	150±5	MLP 2.0 22 AWG F-S 150 mm
2298101224	300±5	MLP 2.0 22 AWG F-S 300 mm

- NOTE:
1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
 2. THE PRODUCT SPECIFICATION RELIES ON THE TERMINALS & WIRE SPEC.
 3. FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. TINNING DIA MUST BE 1MM MAX.

REVISION	CHANGE NOTE	EC NO	DATE	CUSTOMER P/N	CUSTOMER REV
A1	TINNING DIA IS UPDATED	ER	13-JUN-2025	NA	NA
A	INITIAL RELEASE	ER	13-MAY-2025	NA	NA

DETAIL	DESCRIPTION	DETAIL	DESCRIPTION
	Continues Taping		PVC sleeve or Silicon sleeve
	HST		T Dimension
	Woven Braid		Convulated Tube
	Spot Taping		Customer Specific requirements

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
	DIMENSION UNITS: mm SCALE: NTS
	GENERAL TOLERANCES (UNLESS SPECIFIED)
	ANGULAR TOL ± °
DIVISIONAL SYMBOLS	CURRENT REV DESC:
	4 PLACES ±
	3 PLACES ±
	2 PLACES ±
	1 PLACE ±
	0 PLACES ±
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION
	DRAWING: A3-SIZE
	SERIES: 229810
	MATERIAL NUMBER: SEE TABLE
	CUSTOMER: GENERAL MARKET
	SHEET NUMBER: 1 OF 1

molex

SEE TABLE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER: 2298101222

DOC TYPE: PSD

DOC PART: 000

REVISION: A1