

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	TE STANDARD	16JUL2024	NM	RB




NOTES
Bemerkungen

1 TE-CONNECTIVITY ORDER-NUMBER
TE-Connectivity Bestellnummer

MOUNTING DETAIL:
Montagebohrung

WITH LOCKING RING
mit Nasenscheibe



WITHOUT LOCKING RING
ohne Nasenscheibe



ISO 1:2


KEYWAY
Nutseite

OPPOSITE KEYWAY
Nutgegenseite



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
DIN ISO 2768 cL

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

DWN Pavan R R 15JUL2024
CHK N.Mielke 15JUL2024
APVD R.Baumgartner 15JUL2024
PRODUCT SPEC
APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME
TOGGLE SWITCH
Kippschalter

SIZE A3 CAGE CODE 00779 DRAWING NO. C-08-2-1-24_G RESTRICTED TO -

SCALE 1:1 SHEET 1 OF 2 REV A

