






MODEL NUMBER	"A"	INTERFACE PER
CBBJ79-G	9/16	MIL-STD-348 FIG. 201-2
CBBJ79S-G	5/8 w/3X Ø.047 SAFETY WIRE HOLES	
CBBJ79TL-G	9/16	
CBBJ79TLS-G	5/8 w/3X Ø.047 SAFETY WIRE HOLES	
CBBJ79FL-G	9/16	
CBBJ79FLS-G	5/8 w/3X Ø.047 SAFETY WIRE HOLES	
CBBJ379-G	9/16	MIL-STD-348 FIG. 202-2
CBBJ379S-G	5/8 w/3X Ø.047 SAFETY WIRE HOLES	


REV	ECO	DATE
001	60388	11/10/2025



CBBJ79-G SHOWN



CBBJ79TL-G SHOWN



CBBJ79FL-G SHOWN



CBBJ379-G SHOWN

NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL & FINISH:

- 1.1 BODY: GOLD PLATED BRASS
- 1.2 INSULATOR & DIELECTRIC: PTFE (TEFLON)
- 1.3 INTERMEDIATE CONTACT: GOLD PLATED BRASS
- 1.4 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
- 1.5 GASKET: SILICONE RUBBER
- 1.6 MOUNTING HARDWARE: GOLD PLATED COPPER ALLOY

2. ELECTRICAL:

- 2.1 FREQUENCY (MAX): 500 MHZ
- 2.2 IMPEDANCE: NON-CONSTANT

3. PANEL NUT TORQUE (MAX): 35 INCH POUNDS

4. PANEL THICKNESS (MAX): .109

NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018	Model No:	CBBJX79YYZ-G	TROMPETER			
	RoHS2	2015/863/EU	Cage Code	14949	Title: TRB/TRT BULKHEAD CIRCUIT BOARD JACK	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH	3RD ANGLE PROJECTION	ENGINEER:	C. MONAHAN	Drawing No.	3-0379
	ANGLES ±2°	Date:	11/10/2025	Size	A	DO NOT SCALE DRAWING
				Workmanship Std:	TFS-4	Sheet 1 OF 1
				REV.	001	