











⇒ PULL OUT DIRECTION




DETAIL "A"


NOTES

1. RE DETAILED DIMESION, SEE PRODUCT DRAWING.
2. NUMBER OF CONNECTORS : 20,000PCS/REEL
3. LEAD TAPE LENGTH :




4. PEEL OFF FORCE OF THE TOP TAPE IS DEFINDED BY IEC 60286-3.
5. MATERIAL
 - CARRIER TAPE : POLYSTYRENE OR PET
 - TOP TAPE : PET, OTHER
 - REEL : POLYSTYRENE(PS) [RECYCLE MATERIAL CONTAINED]

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex			
mm		1:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)				0.35 BB CONN H=0.6 ACB6 PLUS PLUG PKG							
ANGULAR TOL ± 1.0 °											
4 PLACES		± 0.05		EC NO: 837764		2025/09/24					
3 PLACES		± 0.05		DRWN: JACKSM7							
2 PLACES		± 0.05		CHK'D: MRAMAKRISHNA							
1 PLACE		± 0.1		APPR: YNAITO		2025/10/27					
0 PLACES		± 0.2		INITIAL REVISION:		PRODUCT CUSTOMER DRAWING					
DRWN: JACKSM7				2025/09/24		DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION
APPR: YNAITO				2025/10/27		2167010003-SD		PSD		000	A
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
				A3-SIZE		216701		SEE SHEET2		CUSTOMER	
								GENERAL		SHEET NUMBER	
										1 OF 2	



12.31	11.50	24.00	2167010608	60
11.26			2167010548	54
10.56			2167010508	50
8.81			2167010408	40
7.06	9.25	16.00	2167010308	30
6.01			2167010248	24
5.34			2167010208	20
3.56			2167010108	10
H	J	G	EMBOSSED TAPE PACKAGE	Ckts
			ORDER No.	
			CONNECTOR SERIES No. : 216701****	
DOCUMENT STATUS	P1	RELEASE DATE	2025/10/27	08:00:17

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex				
mm		5:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
ANGULAR TOL ± 1.0 °											
4 PLACES		± 0.05		EC NO: 837764			0.35 BB CONN H=0.6 ACB6 PLUS PLUG PKG				
3 PLACES		± 0.05		DRWN: JACKSM7 2025/09/24							
2 PLACES		± 0.05		CHK'D: MRAMAKRISHNA 2025/10/27							
1 PLACE		± 0.1		APPR: YNAITO 2025/10/27			PRODUCT CUSTOMER DRAWING				
0 PLACES		± 0.2		INITIAL REVISION:			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRWN: JACKSM7 2025/09/24		2167010003-SD		PSD	000	A	
				APPR: YNAITO 2025/10/27							
				DRAWING		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A3-SIZE		216701		GENERAL		2 OF 2	



SMALL PACKAGE

⇒ PULL OUT DIRECTION

REEL


A

DETAIL "A"

NOTES

- RE DETAILED DIMENSION, SEE PRODUCT DRAWING.
- NUMBER OF CONNECTORS : 20,000PCS/REEL
- LEAD TAPE LENGTH :
100 MIN. TOP TAPE BONDED PART (EMPTY)
400 MIN. TOP TAPE LEADER PART
160 MIN. TAIL PART (EMPTY)
COMPONENT SUPPLIER
- PEEL OFF FORCE OF THE TOP TAPE IS DEFINED BY IEC 60286-3.
- MATERIAL
 - CARRIER TAPE : POLYSTYRENE OR PET
 - TOP TAPE : PET, OTHER
 - REEL : POLYSTYRENE(PS) [RECYCLE MATERIAL CONTAINED]

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
FA=0 FE=0 FF=0		DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 837876 DRWN: JSLEE042025/10/20 CHK'D: JSLEE042025/10/20 APPR: JBJIN2025/10/21 INITIAL REVISION: DRWN: JSLEE042025/10/20 APPR: JBJIN2025/10/21 THIRD ANGLE PROJECTION A3-SIZE216701						0.35 BB CONN H=0.6 ACB6 PLUS PLUG PKG					
		mm		1:1													
DIVISIONAL SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)										PRODUCT CUSTOMER DRAWING					
		ANGULAR TOL ± 1.0 °															
		4 PLACES		± 0.05		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION					
		3 PLACES		± 0.05		2167010008-SD		PSD		000		A					
		2 PLACES		± 0.05													
1 PLACE		± 0.1		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER									
0 PLACES		± 0.2		SERIES		GENERAL		1 OF 2									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																	



12.31	11.50	24.00	2167010608	O	---	60
11.26			2167010548	O	---	54
10.56			2167010508	O	---	50
8.81			2167010408	O	---	40
7.06	9.25	16.00	2167010308	O	---	30
6.01			2167010248	O	---	24
5.34			2167010208	O	---	20
3.56			2167010108	O	---	10
H	J	G	EMBOSSSED TAPE PACKAGE	HIGH VOL. TOOL	LOW VOL. TOOL	Ckts
			ORDER No.	SAMPLE PREPARATION		
				O : TOOLED		
				□ : WORK PROCESS		
		--- : TOOLING TO BE CONFIRMED				
CONNECTOR SERIES No. : 216701****						
DOCUMENT STATUS	P1	RELEASE DATE	2025/10/21	00:24:02		

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex						
	mm		5:1												
	GENERAL TOLERANCES (UNLESS SPECIFIED)								0.35 BB CONN H=0.6 ACB6 PLUS PLUG PKG						
	ANGULAR TOL ± 1.0 °														
	4 PLACES ± 0.05		EC NO: 837876		2025/10/20										
	3 PLACES ± 0.05		CHK'D: JSLEE04		2025/10/20										
	2 PLACES ± 0.05		APPR: JBJIN		2025/10/21										
	1 PLACE ± 0.1		INITIAL REVISION:				DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION			
	0 PLACES ± 0.2		DRWN: JSLEE04		2025/10/20		2167010008-SD		PSD		000	A			
	APPR: JBJIN		2025/10/21		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SEE SHEET2		GENERAL		2 OF 2	
						A3-SIZE		216701							