


COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



3	2	High power contact	FMP006S103K	20A / AWG 12-16
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C to +130°C) acc. UL94V-0	black
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
▽ = 0 ▽ = 0 ▽ = 0		DIMENSION UNITS		SCALE		MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-mK				molex					
		mm		2:1											
						CURRENT REVISION				FCT D-Sub Mixed-Layout Connector					
				DRWN: DRAWN BY msteinbrueck 23-01-2024											
				APPR: APPR BY mteubel 30-01-2024											
		3		24130		INITIAL REVISION				PRODUCT CUSTOMER DRAWING					
		2		23933											
		1				MATERIAL NUMBER				REVISION					
		REV.		CH.-NO.											
						DRWN: DRAWN BY Markus.Jobst 10-05-2010				1731070785					
				APPR: APPR BY birgit.rinder 11-05-2010				3							
REPLACEMENT FOR:				FRIST ANGLE PROJECTION		DRAWING		DOCUMENT NUMBER				CUSTOMER		SHEET NUMBER	
						A3-SIZE		F2W2S-0947				GENERAL MARKET		1 OF 1	