



	10	9	8	7	6	5	4	3	2	1					
F	MATERIAL NO., LOOSE PC	ENGINEERING P/N	MATERIAL NO. (TAPE)	ENGINEERING P/N	W ±.010	C MIN	"L" MAX	THKNS, REF	S ±.005	H NOMINAL					
	190670001	D-950-06	----	----	.468/11.89	.380/9.65	1.41 (35.8)	.045/1.14	.146/3.71	-					
	190670003	D-950-08	190670005	D-950-08T	.468/11.89	.380/9.65	1.41 (35.8)	.045/1.14	.173/4.39	1.07/27.2					
	190670006	D-950-10	190670007	D-950-10T	.468/11.89	.380/9.65	1.41 (35.8)	.045/1.14	.198/5.03						
	190670008	D-950-14	190670011	D-950-14T	.468/11.89	.380/9.65	1.41 (35.8)	.045/1.14	.265/6.73						
	190670012	D-950-56	190670013	D-950-56T	.468/11.89	.380/9.65	1.41 (35.8)	.045/1.14	.328/8.33						
	190670016	D-951-10	190670017	D-951-10T	.588/14.94	.445/11.30	1.54 (39.1)	.045/1.14	.198/5.03	1.07/27.2					
	190670018	D-951-14	----	----	.588/14.94	.445/11.30	1.54 (39.1)	.045/1.14	.265/6.73	-					
E	190670025	D-951-56	190670026	D-951-56T	.588/14.94	.445/11.30	1.54 (39.1)	.045/1.14	.328/8.33	1.07/27.2					
	190670022	D-951-38	190670024	D-951-38T	.588/14.94	.445/11.30	1.54 (39.1)	.045/1.14	.390/9.91						
	190670128	D-951-76	----	----	.588/14.94	.445/11.30	1.54 (39.1)	.045/1.14	.453/11.51	-					
	-----	-----	-	-	.810/20.57	.628/15.95	1.84 (46.7)	.050/1.27	.390/9.91	-					
	-----	-----	-	-	.810/20.57	.628/15.95	1.84 (46.7)	.050/1.27	.453/11.51	-					
	-----	-----	-----	-----	.810/20.57	.628/15.95	1.84 (46.7)	.050/1.27	.515/13.08	1.40/35.6					
	-----	-----	----	----	.810/20.57	.628/15.95	1.84 (46.7)	.050/1.27	.656/16.66	-					
	190670032	D-953-12	-	-	1.125/28.58	1.005/25.53	2.37 (60.2)	.050/1.27	.515/13.08	-					
	190670034	D-953-58	-	-	1.125/28.58	1.005/25.53	2.37 (60.2)	.050/1.27	.656/16.66	-					
D	190670033	D-953-34	-	-	1.125/28.58	1.005/25.53	2.37 (60.2)	.050/1.27	.781/19.84	-					
	190670035	D-956-06	----	----	.374/9.50	.380/9.65	1.36 (34.5)	.045/1.14	.146/3.71	-					
	190670037	D-956-08	190670038	D-956-08T	.374/9.50	.380/9.65	1.36 (34.5)	.045/1.14	.173/4.39	1.07/27.2					
	190670039	D-956-10	190670040	D-956-10T	.374/9.50	.380/9.65	1.36 (34.5)	.045/1.14	.198/5.03						
	190670041	D-956-14	190670042	D-956-14T	.374/9.50	.380/9.65	1.36 (34.5)	.045/1.14	.265/6.73						
C															
B	 FOR TAPE APPLIED PART NUMBERS														
A	NOTE(S): 1. MATERIAL: ITEM ① - COPPER, ELECTRO-TIN PLATED ITEM ② - MOLDED NYLON, RED 2. ASSEMBLY IS RoHS COMPLIANT. 3. MWID = MAXIMUM WIRE INSULATION DIAMETER.														
<table><tr><td>DOCUMENT STATUS</td><td>P1</td><td>RELEASE DATE</td><td>2024/11/19</td><td>08:37:16</td></tr></table>											DOCUMENT STATUS	P1	RELEASE DATE	2024/11/19	08:37:16
DOCUMENT STATUS	P1	RELEASE DATE	2024/11/19	08:37:16											
	9	8	7	6	5	4	3	2	1						