


MATERIAL NO. (LOOSE PIECE)	ENGINEERING NO. (LOOSE PIECE)	MATERIAL NO. (TAPE MOUNTED)	ENGINEERING NO. (TAPE MOUNTED)	STUD SIZE	"S" ± .005 (0.13)	DIM "B" ±.005(0.13)	DIM "C"	DIM "L"	DIM "W"
190980041	BB-1707-05	190980042	BB-1707-05T	5	.127(3.23)	.105/2.67	.230/5.84	.585/14.86	.265/6.73
190980043	BB-1707-06	190980044	BB-1707-06T	6	.146(3.71)	.114/2.90	.230/5.84	.585/14.86	.265/6.73
190980047	BB-1716-08	190980048	BB-1716-08T	8	.173(4.39)	.139/3.53	.261/6.63	.646/16.41	.320/8.13
190980049	BB-1717-10	190980050	BB-1717-10T	10	.198(5.03)	.156/3.96	.261/6.63	.694/17.63	.340/8.64







PARTS ON TAPE

NOTE(S):

1. MATERIAL: COPPER .031 (0.79) THICK
2. PLATING: ELECTRO-TIN
3. PARTS ARE RoHS COMPLIANT

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FP = 0
DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS: IN/MM
SCALE: 10:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: DIM WAS MAX

EC NO: 836568
DRWN: DEANNM1 2025/10/03
CHK'D: ETHRODAHL 2025/10/06
APPR: ETHRODAHL 2025/10/06

INITIAL REVISION:
DRWN:
APPR:

molex

SNAP SPADE TONGUE TERMINAL, 16-14 AWG

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-19098-004	PSD	001	B2

THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	C-SIZE	19098	SEE CHART	GENERAL MARKET	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2025/10/06 13:43:58

FORMAT: Eng-lega-master-tb-prod-C
REVISION: E1
DATE: 2021/05/01