

10	9	8	7	6	5	4	3	2	1					
MAT'L NO (LOOSE PC)	ENG NO (LOOSE PC)	MAT'L NO (ON STRIP)	ENG NO (ON STRIP)	MAT'L NO (ON TAPE)	ENG NO (ON TAPE)	WIRE GAGE	FITS MALE TAB	COLOR	"A" MAX	Ø"B" MIN	"C" MAX	MWID	"E" MAX	"H" REF
190030071	M-2212	190030106	M-2212C	190030073	M-2212T	26-24	.250 x .032 (6.35 x 0.81)	YELLOW	.86 (21.8)	.028 (0.71)	.38 (9.7)	.075 (1.91)	.18 (4.6)	1.42 (36.1)
190030064	M-2210	190030103	M-2210C	190030067	M-2210T		.187 x .020 (4.75 x 0.51)	YELLOW	.78 (19.8)		.32 (8.1)		.16 (4.1)	1.38 (35.1)
190030068	M-2211	190030104	M-2211C	190030070	M-2211T		.187 x .032 (4.75 x 0.81)	DK YELLOW						
190030001	AA-2201	190030105	AA-2201C	190030003	AA-2201T	22-18	.250 x .032 (6.35 x 0.81)	SALMON	.86 (21.8)	.056 (1.42)	.38 (9.7)	.135 (3.43)	.18 (4.6)	1.42 (36.1)
190030036	AA-2213	190030109	AA-2213C	190030074	AA-2213T		.205 x .020 (5.21 x 0.51)	SALMON	.78 (19.8)		.32 (8.1)		.16 (4.1)	1.38 (35.1)
190030038	AA-2214	190030110	AA-2214C	190030075	AA-2214T		.205 x .032 (5.21 x 0.81)	PINK						
190030011	AA-2202	190030107	AA-2202C	190030013	AA-2202T		.187 x .020 (4.75 x 0.51)	SALMON						
190030017	AA-2203	190030108	AA-2203C	190030020	AA-2203T		.187 x .032 (4.75 x 0.81)	PINK						
190030024	AA-2204	190030097	AA-2204C	190030026	AA-2204T		.110 x .020 (2.79 x 0.51)	SALMON						
190030030	AA-2205	190030098	AA-2205C	190030032	AA-2205T		.110 x .032 (2.79 x 0.81)	PINK		.23 (5.8)	.15 (3.8)	1.39 (35.3)		
190030040*	BB-2206	190030041*	BB-2206C	190030042*	BB-2206T	16-14	.250 x .032 (6.35 x 0.81)	BLUE	.86 (21.8)	.079 (2.01)	.38 (9.7)	.160 (4.06)	.18 (4.6)	1.41 (35.8)
190030062*	BB-2215	190030085*	BB-2215C	190030077*	BB-2215T		.205 x .020 (5.21 x 0.51)	BLUE	.78 (19.8)		.32 (8.1)		.17 (4.3)	
190030063*	BB-2216	190030086*	BB-2216C	190030078*	BB-2216T		.205 x .032 (5.21 x 0.81)	AQUA						
190030050*	BB-2207	190030051*	BB-2207C	190030052*	BB-2207T		.187 x .020 (4.75 x 0.51)	BLUE						
190030056*	BB-2208	190030057*	BB-2208C	190030058*	BB-2208T		.187 x .032 (4.75 x 0.81)	AQUA						
196060002	C-2293	196060001	C-2293C	196060003	C-2293T	12-10	.250 x .032 (6.35 x 0.81)	YELLOW	1.03 (26.2)	.117 (2.97)	.38 (9.7)	.235 (5.97)	.22 (5.6)	1.53 (38.9)
CONTINUOUS PLASTIC STRIP Ø"B" NEMA DETENT LOCATION "C" TERMINAL CUT-OFF LOCATION, MAY PROTRUDE FROM HOUSING WIRE STOP Ø MWID "A" "E" 4 G2 ASSY P/N'S WITH AN ASTERISK "*" ONLY. (HOUSING FEATURES AS SHOWN)														
PARTS ON TAPE														
NOTE(S): 1. MATERIAL: TERMINAL: TIN PLATED BRASS FERRULE: TIN PLATED BRASS INSULATION: NYLON 6/6 94V-2, SEE CHART FOR COLOR. 2. MWID = MAXIMUM WIRE INSULATION DIAMETER. 3. MUST BE RoHS COMPLIANT. 4 THIN MEMBRANE MAY BE PRESENT IN TAB CUT-OUT.														
DOCUMENT STATUS	P1	RELEASE DATE	2026/01/14	15:13:24										
FUNCTIONAL SYMBOLS THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION FA= 0 FC= 0 FD= 0 DIVISIONAL SYMBOLS DIMENSION UNITS SCALE GENERAL TOLERANCES (UNLESS SPECIFIED) 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ± ANGULAR TOL ± ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS CURRENT REV DESC: ADDED FLAG 4 EC NO: 844661 DRWN: DEANNM1 CHK'D: ETHRODAHL APPR: ETHRODAHL INITIAL REVISION: DRWN: BENDERLE APPR: RDEROSS THIRD ANGLE PROJECTION DRAWING SERIES MATERIAL NUMBER CUSTOMER SHEET NUMBER INCH/MM NTS MM INCH 2026/01/12 2026/01/14 2026/01/14 2002/04/02 2002/04/03 B-SIZE 19003 SEE CHART GENERAL MARKET 1 OF 1 molex INSULKRIMP FEMALE FIQD STANDARD FLARE PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER DOC TYPE DOC PART REVISION SD-19003-005 PSD 001 G2														
FORMAT: Eng-lega-master-lb-prod-B REVISION: E DATE: 2020/1/14														