


12		11		10		9		8		7		6		5		4		3		2		1	
UNPLATED MATERIAL NUMBER	UNPLATED ENG. NUMBER	UNPLATED MAT. NO. ON TAPE	UNPLATED ENG. NO. ON TAPE	PLATED MATERIAL NUMBER	PLATED ENGINEERING NUMBER	PLATED MAT. NO. ON TAPE	PLATED ENG. NO. ON TAPE	SEE DETAIL	STUD SIZE	WIRE RANGE	"S" ±.015/0.38	"L" ±.050/1.27	"W" ±.050/1.27	"C" ±.050/1.27	"B" ±.020/0.51	"T" ±.020/0.51							
H	1922 10408	BCL-8 10	---	---	1922 10223	BCL-8 10-PL	1908200 11	BCL-8 10-PLT	A	10/4.8mm	8 AWG/10mm ²	.214/5.45	1.187/30.15	.438/11.13	.376/9.55	.185/4.70	.070/1.78	H					
	1922 10409	BCL-8 14	1908200 14	BCL-8 14T	1922 10224	BCL-8 14-PL	1908200 13	BCL-8 14-PLT	A	1/4"/M6	8 AWG/10mm ²	.278/7.06	1.187/30.15	.438/11.13	.376/9.55	.185/4.70	.070/1.78						
	1922 10562	BCL-8 14-WP	---	---	1922 10563	BCL-8 14-WP-PL	---	---	---	1/4"/M6	8 AWG/10mm ²	.278/7.06	1.313/33.35	.594/15.09	.422/10.72	.185/4.70	.070/1.78						
	1922 104 11	BCL-85 16	---	---	1922 10225	BCL-85 16-PL	1908200 16	BCL-85 16-PLT	A	5/16"/M8	8 AWG/10mm ²	.340/8.63	1.187/30.15	.438/11.13	.376/9.55	.185/4.70	.070/1.78						
	1922 10482	BCL-85 16-WP	---	---	1922 10483	BCL-85 16-WP-PL	190820034	BCL-8516-WP-PLT	B	5/16"/M8	8 AWG/10mm ²	.340/8.63	1.313/33.35	.594/15.09	.422/10.72	.185/4.70	.070/1.78						
	1922 104 10	BCL-838-WP	1908200 15	BCL-838-WPT	1922 10226	BCL-838-WP-PL	192210566	BCL-838-WP-PLT	B	3/8"/M9	8 AWG/10mm ²	.400/10.16	1.313/33.35	.594/15.09	.422/10.72	.185/4.70	.070/1.78						
	1922 1048 1	BCL-838-XWP	---	---	1922 10484	BCL-838-XWP-PL	---	---	---	3/8"/M9	8 AWG/10mm ²	.400/10.16	1.469/37.31	.766/19.46	.394/10.01	.185/4.70	.070/1.78						
G	1922 104 15	BCL-8 12-XWP	---	---	1922 104 14	BCL-8 12-XWP-PL	---	---	---	1/2"/M12	8 AWG/10mm ²	.520/13.21	1.469/37.31	.766/19.46	.394/10.01	.185/4.70	.070/1.78	G					
	1922 10425	BCL-6 10	---	---	1922 10424	BCL-6 10-PL	190820003	BCL-6 10-PLT	c	10/4.8mm	6 AWG/16mm ²	.214/5.45	1.281/32.54	.438/11.13	.381/9.68	.232/5.89	.075/1.90						
	1922 10406	BCL-6 14-WP	---	---	1922 10227	BCL-6 14-WP-PL	190820005	BCL-6 14-PLT	B	1/4"/M6	6 AWG/16mm ²	.278/7.06	1.406/35.72	.594/15.09	.427/10.85	.232/5.89	.080/2.03						
	1922 10494	BCL-6 14	---	---	1922 10495	BCL-6 14 -PL	1922 10498	BCL-6 14 1-PLT	c	1/4"/M6	6 AWG/16mm ²	.278/7.06	1.281/32.54	.438/11.13	.381/9.68	.232/5.89	.075/1.90						
	1922 10407	BCL-65 16-WP	---	---	1922 10228	BCL-65 16-WP-PL	190820009	BCL-65 16-PLT	B	5/16"/M8	6 AWG/16mm ²	.340/8.63	1.406/35.72	.594/15.09	.427/10.85	.232/5.89	.080/2.03						
	1922 10493	BCL-65 16	1908200 10	BCL-65 16T	1922 10492	BCL-65 16-PL	---	---	c	5/16"/M8	6 AWG/16mm ²	.340/8.63	1.281/32.54	.438/11.13	.381/9.68	.232/5.89	.075/1.90						
	1922 10384	BCL-638-WP	---	---	1922 10229	BCL-638-WP-PL	190820007	BCL-638-PLT	B	3/8"/M9	6 AWG/16mm ²	.400/10.16	1.406/35.72	.594/15.09	.427/10.85	.232/5.89	.080/2.03						
---	---	---	---	---	---	---	---	---	3/8"/M9	6 AWG/16mm ²	.400/10.16	1.563/39.70	.766/19.46	.472/11.99	.232/5.89	.080/2.03							
	1922 104 17	BCL-6 12-XWP	---	---	1922 104 16	BCL-6 12-XWP-PL	---	---	---	1/2"/M12	6 AWG/16mm ²	.520/13.21	1.563/39.70	.766/19.46	.472/11.99	.232/5.89	.080/2.03						



B	NOTES: 1. FOR INSPECTION SIGHT HOLE, PLEASE CONSULT FACTORY. 2. OTHER STUD SIZES MAY BE AVAILABLE, PLEASE CONSULT FACTORY. 3. MATERIAL: COPPER PLATING: TIN 4. MARKINGS CAN BE AT EITHER LOCATION SHOWN. 5. IF TONGUE IS TO BE BENT AT ANY ANGLE, IT MUST BE BENT AROUND A RADIUS ONE HALF THE TONGUE THICKNESS. 6. ALL PARTS ARE RoHS COMPLIANT.					A																																																																																			
	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																								
	<table> <tr> <td rowspan="2">DIMENSION UNITS</td><td colspan="2">SCALE</td><td colspan="2" rowspan="2">CURRENT REV DESC: ADDED PN 190820034</td><td colspan="2" rowspan="2"> molex </td></tr> <tr> <td>INCH/MM</td><td>NTS</td></tr> <tr> <td colspan="3" rowspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2" rowspan="2"> EC NO: 758223 DRWN: DEANNM1 2023/07/31 CHK'D: ETHRODAHL 2023/07/31 APPR: ETHRODAHL 2023/07/31 </td><td colspan="2" rowspan="7"> EYELET STYLE COPPER TERMINALS 8 AND 6 AWG LUGS </td></tr> <tr> </tr> <tr> <td rowspan="2"></td><td></td><td>MM</td><td>INCH</td><td colspan="3" rowspan="2"> PRODUCT CUSTOMER DRAWING </td></tr> <tr> <td>4 PLACES</td><td>±</td><td>±</td></tr> <tr> <td></td><td>3 PLACES</td><td>±</td><td>±</td><td colspan="3" rowspan="2"> INITIAL REVISION: DRWN: DMYRICK 2005/05/03 APPR: RDEROSS 2005/05/03 </td></tr> <tr> <td></td><td>2 PLACES</td><td>±</td><td>±</td></tr> <tr> <td></td><td>1 PLACE</td><td>±</td><td>±</td><td colspan="3"> <table> <tr> <td>DOCUMENT NUMBER</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr> <tr> <td>SD-19221-001</td><td>PSD</td><td>001</td><td>M2</td></tr> </table> </td></tr> <tr> <td></td><td>0 PLACES</td><td>±</td><td>±</td></tr> <tr> <td colspan="3">ANGULAR TOL</td><td>±</td><td>°</td><td colspan="2"> <table> <tr> <td>MATERIAL NUMBER</td><td>CUSTOMER</td><td>SHEET NUMBER</td></tr> <tr> <td>SEE TABLE</td><td>GENERAL MARKET</td><td>1 OF 1</td></tr> </table> </td></tr> <tr> <td colspan="3">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">THIRD ANGLE PROJECTION</td><td>DRAWING</td><td>SERIES</td></tr> <tr> <td colspan="3"></td><td colspan="2" rowspan="2"> </td><td>C-SIZE</td><td>19221</td></tr> </table>						DIMENSION UNITS	SCALE		CURRENT REV DESC: ADDED PN 190820034		molex		INCH/MM	NTS	GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 758223 DRWN: DEANNM1 2023/07/31 CHK'D: ETHRODAHL 2023/07/31 APPR: ETHRODAHL 2023/07/31		EYELET STYLE COPPER TERMINALS 8 AND 6 AWG LUGS				MM	INCH	PRODUCT CUSTOMER DRAWING			4 PLACES	±	±		3 PLACES	±	±	INITIAL REVISION: DRWN: DMYRICK 2005/05/03 APPR: RDEROSS 2005/05/03				2 PLACES	±	±		1 PLACE	±	±	<table> <tr> <td>DOCUMENT NUMBER</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr> <tr> <td>SD-19221-001</td><td>PSD</td><td>001</td><td>M2</td></tr> </table>			DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION	SD-19221-001	PSD	001	M2		0 PLACES	±	±	ANGULAR TOL			±	°	<table> <tr> <td>MATERIAL NUMBER</td><td>CUSTOMER</td><td>SHEET NUMBER</td></tr> <tr> <td>SEE TABLE</td><td>GENERAL MARKET</td><td>1 OF 1</td></tr> </table>		MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	SEE TABLE	GENERAL MARKET	1 OF 1	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION		DRAWING	SERIES						C-SIZE	19221
DIMENSION UNITS	SCALE		CURRENT REV DESC: ADDED PN 190820034		molex																																																																																				
	INCH/MM	NTS																																																																																							
GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 758223 DRWN: DEANNM1 2023/07/31 CHK'D: ETHRODAHL 2023/07/31 APPR: ETHRODAHL 2023/07/31		EYELET STYLE COPPER TERMINALS 8 AND 6 AWG LUGS																																																																																				
		MM	INCH	PRODUCT CUSTOMER DRAWING																																																																																					
	4 PLACES	±	±																																																																																						
	3 PLACES	±	±	INITIAL REVISION: DRWN: DMYRICK 2005/05/03 APPR: RDEROSS 2005/05/03																																																																																					
	2 PLACES	±	±																																																																																						
	1 PLACE	±	±	<table> <tr> <td>DOCUMENT NUMBER</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr> <tr> <td>SD-19221-001</td><td>PSD</td><td>001</td><td>M2</td></tr> </table>			DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION	SD-19221-001	PSD	001	M2																																																																											
DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION																																																																																						
SD-19221-001	PSD	001	M2																																																																																						
	0 PLACES	±	±																																																																																						
ANGULAR TOL			±	°	<table> <tr> <td>MATERIAL NUMBER</td><td>CUSTOMER</td><td>SHEET NUMBER</td></tr> <tr> <td>SEE TABLE</td><td>GENERAL MARKET</td><td>1 OF 1</td></tr> </table>		MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	SEE TABLE	GENERAL MARKET	1 OF 1																																																																													
MATERIAL NUMBER	CUSTOMER	SHEET NUMBER																																																																																							
SEE TABLE	GENERAL MARKET	1 OF 1																																																																																							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION		DRAWING	SERIES																																																																																			
					C-SIZE	19221																																																																																			
<table> <tr> <td>DOCUMENT STATUS</td><td>P1</td><td>RELEASE DATE</td><td>2023/07/31</td><td>18:54:08</td></tr> </table>					DOCUMENT STATUS	P1	RELEASE DATE	2023/07/31	18:54:08	A																																																																															
DOCUMENT STATUS	P1	RELEASE DATE	2023/07/31	18:54:08																																																																																					

FORMAT: Enig leiga-mættir (fr þjóð-C) REFSNÖL E DATE: 2020/01/14														12		11		10		9		8		7		6		5		4		3		2		1
--	--	--	--	--	--	--	--	--	--	--	--	--	--	----	--	----	--	----	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--	---