






COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.

1		2		3			4		5		6		7		8	
Material-No.	Order-No.	Shell Size / for No. of Contacts		A	B	C	D	E	øF1							
1731110951	FKPP1A	1 / 9		37.4	45.2	23°	2 x □12	15.2	3.3 - 7.5							
1731110952	FKPP2A	2 / 15		45.7	45.2	2 x 23°	3 x □12	15.2	3.3 - 7.5							
1731110953	FKPP3A	3 / 25		59.4	45.2	2 x 30°	3 x □12	15.2	3.3 - 7.5							





max. torque are 35 Ncm
Parts not mounted
FKPP1 with 1 blind plate (Part-No. 3)
FKPP2-3 with 2 blind plates (Part-No. 3)

Recommended assembly:



RoHS compliant



5	2	Screw	Steel	
4	1	Cable clamp	Steel	
3	1/2	Blind plate	Plastic	metallized
2	1	Moveable cover	Plastic	black
1	1	Hood	FKPP Plastic	metallized
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
FUNCTIONAL SYMBOLS F₁ = 0 F₂ = 0 F₃ = 0		DIMENSION UNITS		SCALE		MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-mK		molex FCT Plastic Hood	
		mm		2:1					
						CURRENT REVISION			
						DRWN: DRAWN BY gkrimshandl 20-10-2025			
				APPR: APPR BY mateof 20-10-2025					
				INITIAL REVISION		PRODUCT CUSTOMER DRAWING			
		1		DRWN: DRAWN BY gkrimshandl 20-10-2025		MATERIAL NUMBER		REVISION	
		REV. CH.-NO.		APPR: APPR BY mateof 20-10-2025		see table		1	
		REPLACEMENT FOR:		FRIST ANGLE PROJECTION		DRAWING		DOCUMENT NUMBER	
		FMK1-5_SW				A3-SIZE		FKPP1-3A	
								CUSTOMER	
								GENERAL MARKET	
								SHEET NUMBER	
								1 OF 1	