

© – TE Connectivity. All Rights Reserved.


NOTES:
1. REELS (4000 PCS./ REEL);
2. 6 REEL/BOX
3. SINGLE WEIGHT :0.04 g
4. WEIGHT PER BOX: 3.59 Kg

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECN–26–402700; PLATING UPDATED	02SEP2026	TP	AV



4000 PCS / REEL.





NOTES:
FINISH (PLATING THICKNESS IN MICRO–INCHES)
1 5 MICROINCHES MIN GOLD PLATED,
(10WT%P) MIN OVER NICKEL UNDERPLATED.
50 MICROINCHES MIN OVER COPPER UNDERPLATED

ITEM	DESCRIPTION	MATERIAL	FINISH/PLATING	QUANTITY PER ASSY
1	CONTACT AREA	PHOSPHOR BRONZE	NOTE 1	1
2554545-1				

PARTS LIST

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± 0.1
4 PLC ± –
ANGLES ± 5

MATERIAL: REFER NOTES

FINISH: –

DWN SARGUNAM, YAZHINI 08APR2026
CHK CHEE, TSHUPIN 08APR2026
APVD ZI, WILL 08APR2026
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

CUSTOMER DRAWING

TE Connectivity

NAME: TERMINAL CRIMP MINI–FAKRA JACK
–
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–2554545	—

SCALE	SHEET	REV
1:1	1 OF 1	A1