
© 2023 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	19NOV2024	BS	LET
	A2	PROP 65 NOTE ADDED	26MAR2026	CK	SS

394828-E-LF




SECTION B-B

SCALE 2:1
3D VIEW




394847-E-LF



SECTION A-A

SACLE 2:1
3D VIEW



PART NO.	DIMENSION A	REMARK
394847-E-LF	7.25	DISTANCE 13MM
394828-E-LF	3.25	DISTANCE 9MM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-fH
0 PLC ±- ISO 8015
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: COPPER ALLOY
FINISH: NICKEL PLATED

DWN B S SIDDESH 19NOV2024
CHK S SHARMA 19NOV2024
APVD T LEININGER 19NOV2024
PRODUCT SPEC 108-94886
APPLICATION SPEC 114-94781
WEIGHT -

TE Connectivity

NAME
M12 METAL SHELL, FEMALE, VERT, CAT6A
-
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-394847-E-LF	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 2 | REV A2

© 2023 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTE:

1 PROP 65 WARNING LABEL:

THE WARNING LABEL ON THE PRODUCT OR LOWEST LEVEL PACKAGING.

CHEMICAL NAME: NICKEL AND SOLUBLE NICKEL COMPOUNDS.



WARNING: This product contains nickel and soluble nickel compounds, known to the State of California to cause cancer, birth defects or other reproductive harm." All products for California market will comply with Prop 65 labeling requirements. For more information, visit www.P65Warnings.ca.gov

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: COPPER ALLOY

FINISH: NICKEL PLATED

DWN: B S SIDDESH 19NOV2024
CHK: S SHARMA 19NOV2024
APVD: T LEININGER 19NOV2024
PRODUCT SPEC: 108-94886
APPLICATION SPEC: 114-94781
WEIGHT: -

TE Connectivity

NAME: M12 METAL SHELL, FEMALE, VERT, CAT6A
-
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-394847-E-LF	-

CUSTOMER DRAWING

SCALE 2:1 SHEET 2 OF 2 REV A2