


## High Brightness LED Power Module



### DESCRIPTION

The VLSL50xxA are metal core based high brightness LED power modules, assembled with 12, 24 or 36 HB white LEDs. The colour temperature is cold white in the typical range of 5000 K to 7000 K. The LED's are designed with a clear silicone lens for a butterfly shaped radiation characteristic.

### PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: LED module
- Product series: power
- Angle of half intensity: vertical:  $\pm 35^\circ$ , horizontal:  $\pm 60^\circ$

### FEATURES

- Metal core PCB: Al > 0.75 thickness
- Single side/single layer PCB
- Shiny white surface
- 12, 24 or 36 LED's minimum 82 lm at 350 mA per LED. Max. current per LED 1 A
- Conductive top layer: Cu (min. 18  $\mu\text{m}$ )
- Isolation layer prepreg > 63  $\mu\text{m}$
- Compliant to RoHS directive 2002/95/EC
- ESD withstand voltage: up to 2 kV according to JESD22-A114-B
- Luminous flux and colour binning



### APPLICATIONS

- Streetlight
- Internal lighting in buildings
- Tunnel lights
- General lighting application

### PARTS TABLE

PART	COLOR	LUMINOUS FLUX (at $I_F = 700 \text{ mA typ.}$ )	COLOR TEMPERATURE K	TECHNOLOGY
VLSL5012A	Cold white	$\Phi_V = 1740 \text{ lm}$	5000 to 7000	InGaN
VLSL5024A	Cold white	$\Phi_V = 3480 \text{ lm}$	5000 to 7000	InGaN
VLSL5036A	Cold white	$\Phi_V = 5220 \text{ lm}$	5000 to 7000	InGaN

### ABSOLUTE MAXIMUM RATINGS ( $T_{\text{amb}} = 25^\circ\text{C}$ , unless otherwise specified) VLSL5012A, VLSL5024A, VLSL5036A

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Forward current	Per row	$I_F$	750	mA
Power dissipation VLSL5012A	Total (max.)	$P_{\text{tot}}$	35	W
Power dissipation VLSL5024A		$P_{\text{tot}}$	69	W
Power dissipation VLSL5036A		$P_{\text{tot}}$	104	W
Junction temperature		$T_j$	120	$^\circ\text{C}$
Operating temperature range		$T_{\text{amb}}$	- 40 to + 85	$^\circ\text{C}$
Storage temperature range		$T_{\text{stg}}$	- 40 to + 85	$^\circ\text{C}$

\*\* Please see document "Vishay Material Category Policy": [www.vishay.com/doc?99902](http://www.vishay.com/doc?99902)

### OPTICAL AND ELECTRICAL CHARACTERISTICS <sup>(1)</sup> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) VLSL5012A, COLD WHITE

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous flux per row <sup>(2)</sup>	$I_F = 700\text{ mA}$	$\Phi_V$	760	870	-	lm
Luminous flux total <sup>(2)</sup>	$I_{board} = 2 \times 700\text{ mA}$	$\Phi_V$	1520	1740	-	lm
Color temperature	$I_F = 700\text{ mA}$	TK	5000	-	7000	K
Forward voltage per row	$I_F = 700\text{ mA}$	$V_F$	19	20	23	V
Class A ( $V_{Fmax.} - V_{Fmin.}$ ) all rows <sup>(3)</sup>	$I_F = 700\text{ mA}$	$\Delta V_F$	-	-	0.9	V
Temperature coefficient of $V_F$ per row	$I_F = 350\text{ mA}$	$TC_{V_F}$	-	- 20	-	mV/K
Temperature coefficient of $\Phi_V$	$I_F = 350\text{ mA}$ (per row)	$TC_{\Phi_V}$	-	- 0.4	-	%/K

#### Notes

- <sup>(1)</sup> Forward voltages are tested at a current pulse duration of 1 ms and a tolerance of  $\pm 0.1\text{ V}$ . Luminous flux is measured at a current pulse duration of 25 ms and an accuracy of  $\pm 11\%$ .  
<sup>(2)</sup> Calculated based on single LED unit.  
<sup>(3)</sup>  $V_F$  classes are marked at the LED cluster and represent the technical classification only. The single groups cannot be specifically ordered.

### OPTICAL AND ELECTRICAL CHARACTERISTICS <sup>(1)</sup> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) VLSL5024A, COLD WHITE

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous flux per row <sup>(2)</sup>	$I_F = 700\text{ mA}$	$\Phi_V$	760	870	-	lm
Luminous flux total <sup>(2)</sup>	$I_{board} = 4 \times 700\text{ mA}$	$\Phi_V$	3040	3480	-	lm
Color temperature	$I_F = 700\text{ mA}$	TK	5000	-	7000	K
Forward voltage per row	$I_F = 700\text{ mA}$	$V_F$	19	20	23	V
Class A ( $V_{Fmax.} - V_{Fmin.}$ ) all rows <sup>(3)</sup>	$I_F = 700\text{ mA}$	$\Delta V_F$	-	-	0.9	V
Temperature coefficient of $V_F$ per row	$I_F = 350\text{ mA}$	$TC_{V_F}$	-	- 20	-	mV/K
Temperature coefficient of $\Phi_V$	$I_F = 350\text{ mA}$ (per row)	$TC_{\Phi_V}$	-	- 0.4	-	%/K

#### Notes

- <sup>(1)</sup> Forward voltages are tested at a current pulse duration of 1 ms and a tolerance of  $\pm 0.1\text{ V}$ . Luminous flux is measured at a current pulse duration of 25 ms and an accuracy of  $\pm 11\%$ .  
<sup>(2)</sup> Calculated based on single LED unit.  
<sup>(3)</sup>  $V_F$  classes are marked at the LED cluster and represent the technical classification only. The single groups cannot be specifically ordered.

### OPTICAL AND ELECTRICAL CHARACTERISTICS <sup>(1)</sup> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) VLSL5036A, COLD WHITE

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous flux per row <sup>(2)</sup>	$I_F = 700\text{ mA}$	$\Phi_V$	760	870	-	lm
Luminous flux total <sup>(2)</sup>	$I_{board} = 6 \times 700\text{ mA}$	$\Phi_V$	4560	5220	-	lm
Color temperature	$I_F = 700\text{ mA}$	TK	5000	-	7000	K
Forward voltage per row	$I_F = 700\text{ mA}$	$V_F$	19	20	23	V
Class A ( $V_{Fmax.} - V_{Fmin.}$ ) all rows <sup>(3)</sup>	$I_F = 700\text{ mA}$	$\Delta V_F$	-	-	0.9	V
Temperature coefficient of $V_F$ per row	$I_F = 350\text{ mA}$	$TC_{V_F}$	-	- 20	-	mV/K
Temperature coefficient of $\Phi_V$	$I_F = 350\text{ mA}$ (per row)	$TC_{\Phi_V}$	-	- 0.4	-	%/K

#### Notes

- <sup>(1)</sup> Forward voltages are tested at a current pulse duration of 1 ms and a tolerance of  $\pm 0.1\text{ V}$ . Luminous flux is measured at a current pulse duration of 25 ms and an accuracy of  $\pm 11\%$ .  
<sup>(2)</sup> Calculated based on single LED unit.  
<sup>(3)</sup>  $V_F$  classes are marked at the LED cluster and represent the technical classification only. The single groups cannot be specifically ordered.



## SPECIFICATION OF SINGLE LEDs USED FOR THE MODULES

- VLSL5012A, VLSL5024A, VLSL5036A: LED: VLMW92KYKZ6P7R

LUMINOUS FLUX CLASSIFICATION FOR THE SINGLE LED		
GROUP STANDARD	LUMINOUS FLUX $\Phi_V$ (mlm) CORRELATION TABLE	
	MIN.	MAX.
KY	82 000	97 000
KZ	97 000	112 000

## COLOR RANGE AND COLOR BINNING

VLSL5012A, VLSL5024A, VLSL5036A: 5000 K to 7000 K group 6P to7R





Fig. 1 - Chromaticity Coordinates of Colorgroups

# VLSL5012A, VLSL5024A, VLSL5036A


Vishay Semiconductors High Brightness LED Power Module




## PCB BASIC DESIGN VLSL5012A Dimensions in millimeters



Not indicated tolerances ± 0.15



Drawing-No.: 9.920-6727.03-4  
Issue:1; 11.05.10  
22150




Assembled with all jumpers. Jumpers can be removed according driver design




# VLSL5012A, VLSL5024A, VLSL5036A

High Brightness LED Power Module Vishay Semiconductors

## PCB BASIC DESIGN VLSL5024A Dimensions in millimeters



Not indicated tolerances ± 0.15




technical drawings according to DIN specifications

Drawing-No.: 9.920-6727.02-4

Issue:1; 11.05.10

22151




Assembled with all jumpers. Jumpers can be removed according driver design

# VLSL5012A, VLSL5024A, VLSL5036A



Vishay Semiconductors High Brightness LED Power Module


## PCB BASIC DESIGN VLSL5036A Dimensions in millimeters



Not indicated tolerances ±0.15



Drawing-No.: 9.920-6727.01-4  
 Issue: 1; 11.05.10  
 22152



Assembled with all jumpers. Jumpers can be removed according driver design

### PCB CHARACTERISTICS

- Metal core PCB with typical Al thickness of 800  $\mu\text{m}$
- Prepreg thickness typical 127  $\mu\text{m}$
- Conductive pattern Cu typical 25  $\mu\text{m}$
- Total board thickness: 1 mm  $\pm$  15 %
- Warpage max. 0.75 % of board dimension
- Solder resist on top side
- Shiny white surface
- Galvanic of solder pads pure matte Sn ( $\geq$  0.8  $\mu\text{m}$ ), immersion plated
- Assembled with 12, 24 or 36 VLMW92xxx LED's. LED position accuracy  $\pm$  0.125 mm from middle axis, horizontal tilt max. 2°

### EMISSION CHARACTERISTIC





Fig. 2 - Rel. Luminous Intensity vs. Angular Displacement

### BAR CODE PRODUCT LABEL



- A. Type of component
- B. Manufacturing plant
- C. SEL - selection code (bin):  
e.g.: code for  $V_F$  class (A, B, C)
- D. Batch:  
200707 = year 2007, week 07  
PH19 = plant code
- E. Total quantity



## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.